

January	1,	2024
---------	----	------

Custo	omer and Order Information		
Purchas	e Order *	Tag	
Dealor/	Provider Name *		
Dealer/I			
Purchas	er Name and Contact Information *		
Shippin	g Address *		
User Inf	ormation (<i>if available</i>) Weight	kgs Height cm	* required
oser ini		(y) (iii	,
Base	Chair		
BENTLE	Y Bentley 20° Manual Tilt Wheelchair		\$
(j)	Also available: the lightweight Bentley LT wit	th aluminium frame. See separate order form. pdgmobility.com/blt	
Weid	ht Capacity		
werg	Chair Weight Capacity		
02000		Videb.	
02000	113kg / 250 lbs Capacity Available for 14" to 22" Seat W 136kg / 300 lbs Capacity Available for 14" to 22" Seat W		\$
05006	204kg / 450 lbs Capacity Available for 20" to 32" Seat W		\$
	User Weight Range Required for setup of tilt upli		
02430	_	34kg/75 lbs to 45kg/100 lbs 🛛 02432 45kg/100 lbs to 52kg/115 lbs	
02433		58kg/150 lbs to 90kg/200 lbs	
02436		136kg/300 lbs to 170kg/375 lbs 02438 170kg/375 lbs to 204kg/450 lbs	
Eram	e Options		
			÷
02200	Extended Base with Rear Floor Jacks Lifts Rear Wheels off ground for increased stability. Limited	l ground clearance. Not compatible with Attendant Wheel Lock, HD Anti-Tipper, IV Pole, O2 Holder.	\$
02300	Transit Tie Down System (TTDS)		
	TTDS includes 4 factory-installed transport brackets. TTDS I Not compatible with Seat Widths greater than 22". Tested 1	has been tested according to ANSI/RESNA WC 19. See Owners Manual for complete details.	
		to max. weight capacity of 150kg/500 lbs.	
Seat	Width	Overall chair width is $+9.5$ " with $12/16$ " Rear Wheels and $+10.5$ " with $20/22/24$ " Rear Wheels.	
_	Standard Seat Widths		
		15" Seat Width 🛛 03016 16" Seat Width	
03017		18" Seat Width 🛛 03019 19" Seat Width	
03020		21" Seat Width 🛛 03022 22" Seat Width	\$
		ight Capacity Frame. Extended delivery lead times may apply.	
	23" Seat Width		\$
	_	25" Seat Width	\$
□ 03026 □ 03028	_	27" Seat Width	\$
□ 03028 □ 03031		29" Seat Width Image: 03030 million of the seat Width 32" Seat Width	\$ \$
D 03031		2 Seat Willin	Ş
Seat	Depth		
	Standard Seat Depths (Adjustable)		
04016	16" Seat Depth 🛛 04017 1	17" Seat Depth	
04018	18" Seat Depth 🛛 04019 1	19" Seat Depth	
04020	20" Seat Depth		\$
	Custom Seat Depths		
04021	21" Seat Depth		\$
04022	22" Seat Depth		Ś



Order Form - NZ

Fram	e Colour						
	PDG Premium Colours	View colour swatches o	n PDG's website. pdgr	mobility.com/colors			
05001	Black Shimmer	_	Sky Blue		05016	Poppy Red	
05003	Fine Texture Black	05010	Lollypop Blue		05011	Lollypop Red	
05017	Arctic Grey	05018	Tropical Teal		05019	Tangerine Orange	
05020	Olive Green	05021	Lush Lilac		05012	Bubble Gum Pink	
05022	Leaf Green	05023	Boysenberry Purple		05014	Daffodil Yellow	
05200	Custom Colour Contact Perr	nobil for specifications.					\$
Armr							
06000	No Armrests						
_	Single Post Height Adju	_			_		\$
06111			10"-14" Range		06116	12"-16" Range	
_	Dual Post Height Adjus				_		\$
06211	8"-11" Range	06214	10"-14" Range		06216	12"-16" Range	
	Fixed Height Armrests	(12") Full Length Arm	ipad only.				
06100	Single Post	06200	Dual Post				
J.	Armrest Height If provid	ded, Armrests will be set t	o this height by PDG. If	left blank, the default	setting will b	e used.	
1	Seat Pan to top of Armrest:		Does not include heig	ight of Armpad			
J.	Armrest Position Indica	ate preference for Armres	t position. If left blank, t	the default setting will	be used.		
_	In the interest of maintaining ch	· _ ·	nterferance with other c	chair functions, PDG m		e to accommodate stated preference.	
06401	Rear	06402	Mid		06403	Front	
	Locking Flip-up Armres			-			\$
	Not compatible with Fold-down			le with Full Length an			
06310	Set at 10" Height	_	Set at 11" Height		06312	Set at 12" Height	
06313	Set at 13" Height	06314	Set at 14" Height				
Armp	o a d s						
	Regular Armpads						
07100		07101	Full Length - 2" x 14'	"			
	Waterfall Armpads No		-				\$
07105	• Desk Length - 2" x 10"	_	Full Length - 2" x 14'	"			
	Wide Armpads May inte						\$
07110			Full Length - 3" x 12'	n			
	Gel Armpads May interfe		-				\$
07120	Full Length - 2" x 12"		Full Length - 3.5" x 1	12"			Ŧ
	Contour Arm Trough w		-		ons.		\$
07130	Right (4.5" x 18")		Left (4.5" x 18")				*
Armr	est Options						
		ve Armrests outward by u	p to 1" on each side. Sea	at size does not chang	je. May cause	tilt interference.	
07210	1" Total Additional Width						\$
07211	2" Total Additional Width						\$
	Clothing Guards Not co	ompatible with Flip-up Ar	mrests.				
07310	For Single Post Armrests No	t compatible with 8"-11" I	leight range.				\$
07320	For Dual Post Armrests						\$
	Armrest Extensions N	ot compatible with Flip-u					\$
07400	3" Extension - Forward	07401	3" Extension - Rearw	vard			



Order Form - NZ

Seat	Pan														
08000	No Sea	at Pan													
08001	Solid /	Aluminium	Seat Pa	an Re	equired	for 22" S	Seat De	pth.							\$
Seat	Heig	h t													
Don't				Flag	11							6.1			
> forget	Sele	ct desired So	eat-to-	Floor	Heigi	ητ st	F Heigh	it is adju	ustable	within th	ne range	of the c	hosen Su	ıbframe Plate (Low/High).	
		RW 13"	Lo 14"	w 15"	16"	17"	RW	15"	16"	High 17"	18"	19"	20"		
	ers	12" 🗖			10	17	12"					19	20		
	6" Casters	16"					16"								
	6"	20"	<u> </u>		_		20"								
		22" 24"					22" 24"								
				_											
	ers		Lo				-			High					
	Casters	RW 13"	14"	15"	16" □	17"	RW 16"	15"	16"	17"	18"	19" □	20 "		
	8	24"					24"								
Caste	e r s														
	Uret	hane Caster	f s 8" C	asters a	re comp	oatible o	nly witl	n 16″ an	id 24″ Re	ear Whee	els.				
11061	6" x 1.2	5" Caster size				11081	8" x	1.25"	Caster	size					
11063	6" x 1.5	0" Caster size													\$
11084	8" x 2.0	0" Caster size													\$
	Pneu	imatic Caste	ers 8"	Casters	are con	npatible	only w	ith 16″ a	and 24″	Rear Wh	eels.				
□ 11161		5" Caster size													\$
11181		5" Caster size													\$
		0" Caster size		•			. .								\$
11260		egs 6" x 1.5													\$
11400	Frog L	egs Suspen	sion Fo	orks	Only co	ompatib	le with	16 and	24" Rea	r Wheels	. Requir	es 6" So	ft-Roll Ca	ster.	\$
Rear	Whee	els													
	Com	posite Whe	els												
12012	12" Wh	-] 12016	16"	Wheel	l size					12020 20" Wheel size	
12022	22" Wh	eel size				12024		Wheel							
	Spol	ce Wheels													\$
12120	20" Wh	eel size				12122	22"	Wheel	l size					12124 24" Wheel size	
12224	24" He	avy Duty S	poke V	Vheels	5										\$
<u>,</u>	Rear	Wheel Posi	tion	Indicate	e Rear W	/heel po	sitionin	g prefe	rence. If	left blar	nk, the d	efault se	etting wil	l be used.	
-	In the	interest of main	taining c	hair stal			-		with oth	ner chair	functio	ns, PDG		be able to accommodate stated preference.	
12401	Rear					12402	Mic	1						12403 Front	
Axle	Туре														
13000		Release Rea	ar Ayla												
_	•			:5											
13010	rixed	Rear Axles													
Rear	Tires														
14000	Uretha	ane Tires													
14010		natic Tires	May re	sult in a	finisher	Seat H	eight 1	2" area	ter than	stated					
14020							-	-			ght 1/2 [°]	greater	than stat	ted. Not available with Spoke Wheels.	



Order Form - NZ

Hand	rims Handrims are only available with 20", 22", and 24" Rear Wheels.	
15000	No Handrims	
15010	Standard Aluminium Handrims	
15020	Plastic Coated Handrims Not compatible with Drum Brakes.	\$
15030	Projection Handrims Composite Wheels only. 10 Projections, 30°, 1-1.8" Length.	\$
Whee	el Locks & Brakes	
WIICO	User Wheel Locks	
16010	Push to Lock Dill 1016020 Pull to Lock	
16030	Attendant Wheel Locks (Push to Lock)	\$
16040	User & Attendant Wheel Locks Not compatible with Drum Brakes.	\$
16300	Drum Brakes Available with 12" Composite or 20" Spoke Rear Wheels. Urethane Tires only.	\$
	User-activated Unilateral Wheel Lock Pull to Lock. Availlable up to 22" Seat Width only.	\$
16310	Left Activation I 16311 Right Activation	·
	5	
_	el Lock Options	
L 16100	Wheel Lock Extensions Not compatible with Attendant Wheel Lock.	\$
16200	Hill Holders Requires Pneumatic Rear Tires with Flat-Free Inserts.	\$
Anti-	Tippers	
x 17010	Rear Anti-Tippers Required Safety Option.	\$
17020	Front Anti-Tippers	\$
17030	Heavy Duty Rear Anti-Tippers Provide additional rearward stability for users with excessive movement.	\$
	Not compatible with Attendant Wheel Locks, Rear Floor Jacks, IV Pole, O2 Holder.	
Back	Posts	
Back	Back Post Style	
18010	Stroller Handle Back D 18020 Cane Handle Back Seat Widths of up 22" only. May reduce tilt range.	
	Back Post Height Measured from the Seat Pan to the Handle.	
18425		
	Back Post Folding Fold-down Back is not compatible with Dynamic Rocker Back Interface, Reclining Backrest.	
19220	Fold-down 🛛 19221 Non-folding	
	Seat to Back Angle	
□ 19090	Set at 90° Image: 19098 Set at 98° Image: 19106 Set at 106°	
19114	Set at 114° 🛛 19122 Set at 122°	
Back	Options	
	Angle/Height Adjustable Stroller Handle Not compatible with Headrest Mounting Plate or Cane Handle Back.	\$
19010	Button on Outside 🛛 19011 Button on Inside	
	Endomorph Back Backrest will be narrower than Seat by total of 2x the Offset selected below. Minimum width of Backrest is 12".	\$
18102	1" Offset per side I 18103 1.5" Offset per side I 18104 2" Offset per side	
19210	10" Backrest Extension Not compatible with Angle/Height Adjustable Stroller Handle.	\$
19212	Headrest Mounting Plate	\$
x 19230	Not compatible with Backrest Extension, Angle/Height Adjustable Stroller Handle, Cane Handle Back. Not required if mounting to a solid Back.	
_	Spring Back Suspension Not compatible with Reclining Back.	ć
└ 19240	Seating Dynamics Dynamic Rocker Back Interface Not compatible with Fold-down Back, Spring Back Suspension, 30° Recline, Cane Handle, Standard Upholstery.	\$
	Finished Back Post Height is 4" taller than selected Back Post Height.	



Back Upholstery	
D 20000 No Back Upholstery	
Standard Upholstery Not available with Cane Handle Back.	\$
□ 20418 Short (18" Height) □ 20421 Regular (21" Height) □ 20424 Tall (24" Height)	
Tension Adjustable Upholstery Height of Upholstery is 16". Not available with Cane Handle Back.	
□ 20450 For 14" to 22" Seat Width	\$
□ 20451 For 24" to 32" Seat Width	\$
Position of Upholstery Select the desired position of the top of the Upholstery relative to the Seat Pan.	
22" Back Post 25" Back Post	
Style 17" 18" 19" 20" 21" 22" 23" 24" 25" Style 17" 18" 19" 20" 21"	22" 23" 24" 25"
Short I <td></td>	
Regular Image: Constraint of the second se	
Tension Adj Image: Constraint of the second secon	
Tension Adj	
Tilt Activation	
Attendant Tilt only Select trigger mounting location below. Chairs with 204kg/450 lbs Weight Capacity require two tilt triggers (L and R) for tilt a	ctivation
23011 Right Back Post	ctivation.
User Tilt only Not available for 204kg/450 lbs Weight Capacity. Full Length Arm Pads only. Select trigger mounting location below.	Ś
23021 Right Armrest	Ŷ
	Ś
	Ļ
Image: 23031 Right Back Post Image: 23032 Left Back Post Image: 23041 Right Armrest Image: 23042 Left Armrest	
2304 Night Anniest 23042 Leit Anniest 23110 Tilt Trigger Extension	\$
	Ş
Power Tilt 113kg/50 lbs Weight Capacity. 20° tilt range. Includes 2 batteries for off-chair charging. <u>pdgmobility.com/power-tilt</u> Minimum Seat Width is 15". Power Tilt is compatible with either O2 Holder or IV Pole on the same chair, not both.	
23400 Standard Power Tilt	\$
23410 Power Tilt with Manual Tilt Override Allows for instant manual release of tilt in case of power tilt failure.	\$
Toggle Switch 23421 Installed on Right side 23422 Installed on Left side	
Select Button Switch 23431 Installed on Right side 23432 Installed on Left side	
Control Switch Stealth Egg Switch Stealth Egg Switch	
Optional for Egg Switch: 23445 Swing Away Mounting Hardware Not compatible with all Headrest makes and models.	Ś
Specify Headrest to be used:	•
Recline	
_	
23310 Reclining Backrest (Manual)	\$
30° maximum recline. Not compatible with Backrest Extension, Cane Handle Back, Spring Back Suspension, Fold-down Back, Tension Adjustable Upholste Dynamic Rocker Back. Requires longer Frame. Maximum Seat Depth is 19". Finished Back Post Height is 3" taller than selected Back Post Height.	y,
Front Rigging	
25000 No Front Rigging 25001 Sector Blocks only	
Easy-Out TM Front Rigging Effortless insertion and removal. No Hanger Bracket remains on frame. pdgmobility.com/easy-out	
25410 Fixed 70°	\$
25420 Universal Angle Adjustable (0°-110°) Set at angle: (use increments of 10°)	\$
Adjust angle by loosening one bolt. Tool-free leg-length adjustment. Front Rigging can interfere with casters in the 90-110° settings.	
Swing Away Front Rigging Legacy Design. Not compatible with Easy-Out.	
□ 25130 Swing Away 60° □ 25140 Swing Away 70°	
25200 Swing Away Elevating Legrests Includes Calf Pads.	\$
25300 1" Offset Hangers for Swing Away	\$
25110 Standard Plug In 70° Front Rigging Legacy Design. Not compatible with Easy-Out.	



Order Form - NZ

Footplates	
20010 Composite Footblates	
26020 Aluminium Angle Adjustable Footplates	\$
26030 One Piece Fixed Footplate Available on Plug In Front Rigging only. Requires selection of Composite or Aluminium Angle Adjustable.	\$
26040 One Piece Flip-up Footplate Requires selection of Composite or Aluminium Angle Adjustable.	\$
26050 Interlocking Angle Adjustable Footplates Available for Seat Widths up to 21" only.	\$
	Ŧ
Footrest/Legrest Accessories	
Calf Pads Not compatible with Gel Padding.	
²⁷⁰¹² For Easy-Out TM Front Rigging Includes reinforced premium Calf Pad mount.	\$
27010 For Swing Away Front Rigging	\$
27020 Gel Padding Not compatible with Calf Pad or Easy-Out Front Rigging.	\$
Gel Knee Pads	
 27032 For Easy-Out[™] Angle Adjustable Front Rigging 27030 For Swing Away ELR Front Rigging 	\$ \$
 27030 For Swing Away ELR Front Rigging 27040 Length Adjustable Heel Loops 	\$
	\$
Image: Description of the second strate Sizes greater than 22" are not padded. Image: Miller's Dynamic Footrest Mounts Not compatible with Easy-Out Front Rigging.	Ş
27060 For Standard Plug In Front Rigging	\$
□ 27065 For Swing Away 70° Front Rigging Not available on 13" STF Height.	ş
	,
Front Rigging Extension Tubes	
Regular Extension Tubes	
28010 Short <u>14"-18"</u> for Easy-Out Front Rigging <u>13"-17"</u> for Swing Away and Standard Plug In Front Rigging	
28020 Long <u>18"-24"</u> for Easy-Out Front Rigging <u>15"-19"</u> for Swing Away and Standard Plug In Front Rigging	\$
Extra Strength Extension Tubes (Solid) Available on Plug In Front Rigging only. Not compatible with Swing Away or Easy-Out Front Rigging.	\$
28110 Standard (13"-17") 28120 Long (15"-19")	
Lower Leg Length If provided, Front Rigging will be set to this length by PDG. If left blank, the default setting will be used.	
Seat Pan to Foot Plates: Measured along the length of the Front Rigging. Consider the height of your Seat Cushion.	
Miscellaneous Options	
One-Arm Drive Available with 22" and 24" Composite Rear Wheels, Minimum 17" STE and 18" STE, respectively.	Ś
One-Arm Drive Available with 22" and 24" Composite Rear Wheels. Minimum 17" STF and 18" STF, respectively. Limits Tilt. Not compatible with User & Attendant Wheel Locks, Drum Brakes, Quick Release Rear Axles, Pneumatic Tires.	\$
	\$
Limits Tilt. Not compatible with User & Attendant Wheel Locks, Drum Brakes, Quick Release Rear Axles, Pneumatic Tires.	\$
Limits Tilt. Not compatible with User & Attendant Wheel Locks, Drum Brakes, Quick Release Rear Axles, Pneumatic Tires. 30010 Installed on Right side 30011 Installed on Left side 30012 Large Hand Setup 24" Rear Wheels with 22" Driving Handrim. Spoke Guards Available for 20"-24" Composite Rear Wheels. Made from durable and lightweight aluminium.	\$
Limits Tilt. Not compatible with User & Attendant Wheel Locks, Drum Brakes, Quick Release Rear Axles, Pneumatic Tires. 30010 Installed on Right side 30011 Installed on Left side 30012 Large Hand Setup 24" Rear Wheels with 22" Driving Handrim. Spoke Guards Available for 20"-24" Composite Rear Wheels. Made from durable and lightweight aluminium. 30020 Black 30021 Frame Colour	\$
Limits Tilt. Not compatible with User & Attendant Wheel Locks, Drum Brakes, Quick Release Rear Axles, Pneumatic Tires. 30010 Installed on Right side 30011 Installed on Left side 30012 Large Hand Setup 24" Rear Wheels with 22" Driving Handrim. Spoke Guards 30020 Black 30021 30050 Protective Lower Padding	\$
Limits Tilt. Not compatible with User & Attendant Wheel Locks, Drum Brakes, Quick Release Rear Axles, Pneumatic Tires. 30010 Installed on Right side 30011 30012 Large Hand Setup 24" Rear Wheels with 22" Driving Handrim. Spoke Guards Available for 20"-24" Composite Rear Wheels. Made from durable and lightweight aluminium. 30020 Black 30021 Frame Colour 30050 Protective Lower Padding Stealth Flip Down Abductor Requires Solid Seat Pan.	\$
Limits Tilt. Not compatible with User & Attendant Wheel Locks, Drum Brakes, Quick Release Rear Axles, Pneumatic Tires. 30010 Installed on Right side 30011 Installed on Left side 30012 Large Hand Setup 24" Rear Wheels with 22" Driving Handrim. Spoke Guards Available for 20"-24" Composite Rear Wheels. Made from durable and lightweight aluminium. 30020 Black 30021 Frame Colour 30050 Protective Lower Padding Stealth Flip Down Abductor 830060 Small Pad 3"x4"x3"x2" size 30060 Small Pad 3"x4"x3"x2" size 30062	\$ \$ \$
Limits Tilt. Not compatible with User & Attendant Whee Locks, Drum Brakes, Quick Release Rear Axles, Pneumatic Tires. 30010 Installed on Right side 30012 Large Hand Setup 24" Rear Wheels with 22" Driving Handrim. Spoke Guards Available for 20"-24" Composite Rear Wheels. Made from durable and lightweight aluminium. 30020 Black 30050 Protective Lower Padding Stealth Flip Down Abductor Requires Solid Seat Pan. 30060 30080 Gel Hip Guides Reduces available Seat Width by 2".	\$ \$ \$ \$ \$
Limits Tilt. Not compatible with User & Attendant Wheel Locks, Drum Brakes, Quick Release Rear Axles, Pneumatic Tires. 30010 Installed on Right side 30012 Large Hand Setup 24" Rear Wheels with 22" Driving Handrim. Spoke Guards Available for 20"-24" Composite Rear Wheels. Made from durable and lightweight aluminium. 30020 Black 30050 Protective Lower Padding Stealth Flip Down Abductor Requires Solid Seat Pan. 30060 Small Pad 30080 Gel Hip Guides Reduces available Seat Width by 2". 3010 IV Pole Not compatible with HD Anti Tipper, Rear Floor Jacks, Attendant Wheel Locks.	\$ \$ \$ \$ \$ \$
Limits Tilt. Not compatible with User & Attendant Wheel Locks, Drum Brakes, Quick Release Rear Axles, Pneumatic Tires. 30010 Installed on Right side 30012 Large Hand Setup 24" Rear Wheels with 22" Driving Handrim. Spoke Guards Available for 20"-24" Composite Rear Wheels. Made from durable and lightweight aluminium. 30020 30020 Black 30050 Protective Lower Padding Stealth Flip Down Abductor Requires Solid Seat Pan. 30060 Small Pad 3"x4"x3"x2" size 30060 Gel Hip Guides Reduces available Seat Width by 2". 30110 IV Pole Not compatible with HD Anti Tipper, Rear Floor Jacks, Attendant Wheel Locks.	\$ \$ \$ \$ \$
Limits Tilt. Not compatible with User & Attendant Wheel Locks, Drum Brakes, Quick Release Rear Axles, Pneumatic Tires. 30010 Installed on Right side 30011 Installed on Left side 30012 Large Hand Setup 24" Rear Wheels with 22" Driving Handrim. Spoke Guards Available for 20"-24" Composite Rear Wheels. Made from durable and lightweight aluminium. 30020 Black 30021 Frame Colour 30050 Protective Lower Padding Stealth Flip Down Abductor Requires Solid Seat Pan. 30060 Small Pad 3"x4"x3"x2" size 30062 Large Pad 5"x5"x4"x3" size 30080 Gel Hip Guides Reduces available Seat Width by 2". 30010 IV Pole Not compatible with HD Anti Tipper, Rear Floor Jacks, Attendant Wheel Locks. 30102 02 Holder Not compatible with HD Anti Tipper, Rear Floor Jacks, Attendant Wheel Locks. 30102 Q'Straint Lap Belt Model S5-6329-11. For use with WC-19 Transit Tie Down System. 24"-51" Belt Length.	\$ \$ \$ \$ \$ \$
Limits Tilt. Not compatible with User & Attendant Wheel Locks, Drum Brakes, Quick Release Rear Axles, Pneumatic Tires. 30010 Installed on Right side 30011 30012 Large Hand Setup 24" Rear Wheels with 22" Driving Handrim. Spoke Guards Available for 20"-24" Composite Rear Wheels. Made from durable and lightweight aluminium. 30020 Black 30021 Black 30021 Frame Colour 30050 Protective Lower Padding Stealth Flip Down Abductor Requires Solid Seat Pan. 30060 Small Pad 3"x4"x3"x2" size 30060 Small Pad 3"x4"x3"x2" size 30010 IV Pole Not compatible with HD Anti Tipper, Rear Floor Jacks, Attendant Wheel Locks. 30110 VP Pole Not compatible with HD Anti Tipper, Rear Floor Jacks, Attendant Wheel Locks.	\$ \$ \$ \$ \$ \$ \$ \$ \$



Order Notes

OF-NZ-PDGBENT-01.0