





Cust	omer and Order	In formation							
Purcha	se Order *		Tag						
Dealer/	Provider Name *		<u> </u>						
Purcha	Purchaser Name and Contact Information *								
		Illacion							
Shippin	g Address *								
User Inf	formation (<i>if available</i>)	Weight	kgs Height	cm		* required			
- P.o.c.o	- Chair								
Base	Chair								
	Bentley LT 20° Manua								
240100	Bentley LT 20° Manual Tilt	Wheelchair				\$			
i	Choose the standard B o	entley with a steel fran	ne for agitated or heavier user	'S. See separate o	order form.				
W o i o									
_	ht Capacity								
02000	113kg / 250 lbs Chair W								
п	User Weight Range	_		П					
02430	Up to 34kg/75 lbs	_	4kg/75 lbs to 45kg/100 lbs	_	45kg/100 lbs to 52kg/115 lbs				
□ 02433	52kg/115 lbs to 68kg/150 lb	s 📙 02434 6	8kg/150 lbs to 90kg/200 lbs	02435	90kg/200 lbs to 113kg/250 lbs				
Fram	e Options								
02300	Transit Tie Down Syster	n (TTDS)							
	TTDS includes 4 factory-install	ed transport brackets. TTDS h	nas been tested according to ANSI/RES	NA WC 19. See Own	ners Manual for complete details.				
Seat	Width		Overall chair width is +9.5"	with 12/16" Rear Wh	neels and +10.5" with 20/22/24" Rear Wheels.				
	Standard Seat Widths								
03014	14" Seat Width	□ 03015 1	5" Seat Width	03016	16" Seat Width				
03017	17" Seat Width	03018 1	8" Seat Width	03019	19" Seat Width				
03020	20" Seat Width	03021 2	1" Seat Width	03022	22" Seat Width	\$			
Seat	Depth								
J C a c		(Adiustable)							
04016	Standard Seat Depths 16" Seat Depth	_	7" Seat Depth						
04018	18" Seat Depth	_	9" Seat Depth						
04020	20" Seat Depth		э зеас Берсіі			\$			
- 0.02	Custom Seat Depths					٠			
04021	21" Seat Depth					\$			
04021	22" Seat Depth					\$			
	·					-			
Fram	e Colour								
_	PDG Premium Colours			_					
05001	Black Shimmer	_	ky Blue	_	Poppy Red				
05003	Fine Texture Black	_	ollypop Blue		Lollypop Red				
05017	Arctic Grey	_	ropical Teal	_	Tangerine Orange				
05020	Olive Green	_	ush Lilac	_	Bubble Gum Pink				
□ 05022	Leaf Green	□ 05023 B	oysenberry Purple	05014	Daffodil Yellow				
05200	Custom Colour Contact I	Permobil for specifications.				\$			



Armrests							
06000	No Armrests						
	Height Adjustable Armrests (Single Post)	\$					
06111	8"-11" Range						
06100	Fixed Height Armrests (12") Full Length Armpad only.						
2	Armrest Height If provided, Armrests will be set to this height by PDG. If left blank, the default setting will be used.						
3	Seat Pan to top of Armrest: Does not include height of Armpad						
عر	Armrest Position Indicate preference for Armrest position. If left blank, the default setting will be used.						
7	In the interest of maintaining chair stabily and avoiding interferance with other chair functions, PDG may not be able to accommodate stated preference.						
L 06401	Rear						
Armp	o a d s						
	Regular Armpads						
07100							
	Waterfall Armpads	\$					
07105	Desk Length - 2" x 10"						
	Wide Armpads May interfere with wheels in some tilt configurations.	\$					
07110	Desk Length - 3" x 10"						
	Gel Armpads May interfere with wheels in some tilt configurations.	\$					
07120	Full Length - 2" x 12"						
	Contour Arm Trough with Hand Pad May interfere with wheels in some tilt configurations.	\$					
07130	Right (4.5" x 18")						
Armr	est Options						
	Armrest Wideners Move Armrests outward by up to 1" on each side. Seat size does not change. May cause tilt interference.						
☐ 07210	1" Total Additional Width	\$					
_	2" Total Additional Width	\$					
07310	Clothing Guards Not compatible with 8"-11" Height range.	\$					
	Armrest Extensions Not compatible with Desk Length Armpads.	\$					
□ 07400 3" Extension - Forward □ 2407401 3" Extension - Rearward							
Seat	Pan						
08000	No Seat Pan						
08001	Solid Aluminium Seat Pan	\$					
Seat	Height						
Don't	Select desired Seat-to-Floor Height STF Height is adjustable within the range of the chosen Subframe Plate (Low/High).						
forget							
	RW 13" 14" 15" 16" 17" RW 15" 16" 17" 18" 19" 20"						
	12"						
	50 20" 0						
	24"						
	High RW 13" 14" 15" 16" 17" RW 15" 16" 17" 18" 19" 20"						



Cast	ers	
	Urethane Casters 8" Casters are compatible only with 16" and 24" Rear Wheels.	
11061	6" x 1.25" Caster size	
□ 11063	6" x 1.50" Caster size	\$
11084	8" x 2.00" Caster size	\$
	Pneumatic Casters 8" Casters are compatible only with 16" and 24" Rear Wheels.	
11161	6" x 1.25" Caster size	\$
11181	8" x 1.25" Caster size	\$
11184	8" x 2.00" Caster size	\$
11260	Frog Legs 6" x 1.50" Aluminium Soft-Roll Casters	\$
11400	Frog Legs Suspension Forks Only compatible with 16 and 24" Rear Wheels. Requires 6" Soft-Roll Caster.	\$
Rear	Wheels	
	Composite Wheels	
☐ 12012		
12012		
	Spoke Wheels	\$
☐ 12120	_	,
<u> </u>	Rear Wheel Position Indicate Rear Wheel positioning preference. If left blank, the default setting will be used.	
3	In the interest of maintaining chair stabily and avoiding interferance with other chair functions, PDG may not be able to accommodate stated preference.	
12401	Rear	
Axle	Туре	
☐ 13000	Ouick Release Rear Axles	
13010		
13010	rixeu neai Axies	
Rear	Tires	
14000	Urethane Tires	
<u> </u>	Pneumatic Tires May result in a finished Seat Height 1/2" greater than stated.	
14020	Pneumatic Tires with Flat-Free Inserts May result in a finished Seat Height 1/2" greater than stated. Not available with Spoke Wheels.	
1		
Hand	r i m s Handrims are only available with 20", 22", and 24" Rear Wheels.	
15000	No Handrims	
15010	Standard Aluminium Handrims	
15020	Plastic Coated Handrims Not compatible with Drum Brakes.	\$
15030	Projection Handrims Composite Wheels only. 10 Projections, 30°, 1-1.8" Length.	\$
Whe	el Locks & Brakes	
	User Wheel Locks	
<u> </u>	-	
<u> </u>	Attendant Wheel Locks (Push to Lock)	\$
☐ 16040	User & Attendant Wheel Locks Not compatible with Drum Brakes.	\$
☐ 16300	Drum Brakes Available with 12" Composite or 20" Spoke Rear Wheels. Urethane Tires only.	\$
	User-activated Unilateral Wheel Lock Pull to Lock.	\$
☐ 16310	-	•



Whee	l Lock Opt	i o n s																			
☐ 16100	Wheel Lock Exte	ension	is No	t compat	tible with A	ttendant V	/heel Lo	ck.												\$;
☐ 16200	Hill Holders Requires Pneumatic Rear Tires with Flat-Free Inserts. \$;										
A																					
	Tippers																				
17010	Rear Anti-Tippe	ers Re	equired S	Safety Op	otion.															\$	1
Back	Posts																				
	Back Post Styl	e																			
× 18010	Stroller Handle Bac	:k																			
	Back Post Heig	ght M	Measure	d from th	ne Seat Pan	to the Har	ıdle.														
18425	Short (22")				18431	Tall (25	")														
	Back Post Fold	ding	Fold-do	wn Back	is not com	patible wit	h Reclin	ing Back	rest.												
19220	Fold-down																				
☐ 19090	Seat to Back A	ngle			19098	C	.00				□ 19		.	1060							
☐ 19090 ☐ 19114	Set at 90° Set at 114°				19098	Set at 9 Set at 1	_				L 19	106	Set at	106°							
						Jet ut 1															
Back	Options																				
	Angle/Height	Adjus	table		_	Not co	mpatibl	e with H	leadrest	t Moun	ting Plate.									\$,
19010	Button on Outside				19011	Button															
П	Endomorph B	ack i	Backrest		_				offset se	lected l	_									\$	
☐ 18102 ☐ 19210	1" Offset per side	tomaio				1.5" Off					□ 18	104	2" Offs	et per	side						
19210	10" Backrest Extension Not compatible with Angle/Height Adjustable Stroller Handle. \$																				
1,72,12	19212 Headrest Mounting Plate Not compatible with Backrest Extension, Angle/Height Adjustable Stroller Handle. Not required if mounting to a solid Back.																				
P.a.s.k	ll m h al at a ry	,																			
_	Upholstery																				
20000	No Back Uphols																				
D 20418	Standard Uph Short (18" Height)	oister	у		20421	Regula	r (21" ⊢	laiaht)			□ 20	474	Tall (24	1" Hain	ıht)					\$	
20450	Tension Adjusta	able U	pholsi					ieigiit)				12-1	Tan (2-	Tileig	1111/					\$	
	Position of Up							f the Upl	holsterv	/ relativ	e to the Seat P	an.								· ·	
			,		ck Post					1					25" R	ack Po	ct				
	Style	17"	18"	19"	20" 2	l" 22"	23"	24"	25"		Style		17"	18"	19"	20"	21"	22"	23"	24"	25"
	Short										Short	_									
	Regular Tension Adj										Regula Tall										
	,				•					-	Tension /	Adj									
T;_+/	ctivation																				
1111 7																					
23011	Attendant Tilt Right Back Post	only	Select	-		ocation bel Left Ba															
23011	User Tilt only	Full 1 4	enath Ar			trigger mo			below											\$	
23021	Right Armrest					Left Arı		,												*	
	Attendant & U	lser Ti	it Ful	l Length	Arm Pads o	only. Select	trigger	mountir	ng locat	ions be	low.									\$	
23031	Right Back Post					Left Ba															
23041	Right Armrest				23042	Left An	mrest														

See next page for more options >







	23110	Tilt Trigger Extension	\$
		Power Tilt 113kg/250 lbs Weight Capacity. 20° tilt range. Includes 2 batteries for off-chair charging. pdgmobility.com/power-tilt	
_		Minimum Seat Width is 15". Power Tilt is compatible with either O2 Holder or IV Pole on the same chair, not both.	
		Standard Power Tilt	\$
Ш	23410	Power Tilt with Manual Tilt Override Allows for instant manual release of tilt in case of power tilt failure.	\$
	Selec	Toggle Switch ☐ 23421 Installed on Right side ☐ 23422 Installed on Left side	
>	Contro	ol	
	Switcl	_	
		Optional for Egg Switch: 23445 Swing Away Mounting Hardware Not compatible with all Headrest makes and models. Specify Headrest to be used:	\$
	e c l i		
ш	23310	Reclining Backrest (Manual)	\$
		30° maximum recline. Not compatible with Backrest Extension, Fold-down Back, Tension Adjustable Upholstery, Dynamic Rocker Back. Requires longer Frame. Maximum Seat Depth is 19". Finished Back Post Height is 3" taller than selected Back Post Height.	
	ront	Picaina	
		Rigging	
	25000	No Front Rigging 2425001 Sector Blocks only	
П	25440	Easy-Out TM Front Rigging Effortless insertion and removal. No Hanger Bracket remains on frame. pdgmobility.com/easy-out	•
_	25410 25420	Fixed 70° Universal Angle Adjustable (0° 110°)	\$
_	25420	Universal Angle Adjustable (0°-110°) Set at angle: (use increments of 10°) Adjust angle by loosening one bolt. Tool-free leg-length adjustment. Front Rigging can interfere with casters in the 90-110° settings.	\$
		Swing Away Front Rigging Legacy Design. Not compatible with Easy-Out.	
	25130	Swing Away 60°	
	25200	Swing Away Elevating Legrests Includes Calf Pads.	\$
	25300	1" Offset Hangers for Swing Away	\$
	25110	Standard Plug In 70° Front Rigging Legacy Design. Not compatible with Easy-Out.	
E	ootr	plates	
	26010	Composite Footplates	
	26020	Aluminium Angle Adjustable Footplates	\$
	26030	One Piece Fixed Footplate Available on Plug In Front Rigging only. Requires selection of Composite or Aluminium Angle Adjustable.	\$
	26040	One Piece Flip-up Footplate Requires selection of Composite or Aluminium Angle Adjustable.	\$
	26050	Interlocking Angle Adjustable Footplates Available for Seat Widths up to 21" only.	\$
			Ÿ
F	ootr	rest/Legrest Accessories	
		Calf Pads Not compatible with Gel Padding.	
	27012	For Easy-Out TM Front Rigging Includes reinforced premium Calf Pad mount.	\$
_	27010	For Swing Away Front Rigging	\$
Ш	27020	Gel Padding Not compatible with Calf Pad or Easy-Out Front Rigging.	\$
		Gel Knee Pads	
_	27032	For Easy-Out TM Angle Adjustable Front Rigging	\$
ᆜ		For Swing Away ELR Front Rigging	\$
	27040	Length Adjustable Heel Loops	\$
Ш	27050	Bodypoint Padded Calf Strap	\$
F	r o nt	Rigging Extension Tubes	
		Regular Extension Tubes	
	28010	Short 14"-18" for Easy-Out Front Rigging 13"-17" for Swing Away and Standard Plug In Front Rigging	
	28020	Long 18"-24" for Easy-Out Front Rigging 15"-19" for Swing Away and Standard Plug In Front Rigging	\$





\$

\$

\$

\$

\$

\$



☐ 30060 Small Pad 3"x4"x3"x2" size

Gel Hip Guides Reduces available Seat Width by 2".

Wheelchair Backpack Black with PDG Logo. 17"x14" size.

Adhesive Back Hook Strip, 2" x 30" For Cushion mounting.

30080

30110

30120

30200

30222

30170

BENTLEY LT

MC		January 1, 202
*	Lower Leg Length If provided, Front Rigging will be set to this length by PDG. If left blank, the default setting will be used. Seat Pan to Foot Plates: Measured along the length of the Front Rigging. Consider the height of your Seat Cushion.	
	Scatt an to root rates measured along the length of the riolic higging, consider the length of your sear cashion.	
Misce	ellaneous Options	
	One-Arm Drive Available with 22" and 24" Composite Rear Wheels. Minimum 17" STF and 18" STF, respectively.	\$
	Limits Tilt. Not compatible with User & Attendant Wheel Locks, Drum Brakes, Quick Release Rear Axles, Pneumatic Tires.	
30010	Installed on Right side \Box 30011 Installed on Left side	
30012	Large Hand Setup 24" Rear Wheels with 22" Driving Handrim.	
	Spoke Guards Available for 20"-24" Composite Rear Wheels. Made from durable and lightweight aluminium.	\$
30020	Black	
30050	Protective Lower Padding	\$
	Stealth Flip Down Abductor Requires Solid Seat Pan.	\$

☐ 30062 Large Pad 5"x5"x4"x3" size

IV Pole Not compatible with Attendant Wheel Locks. Requires frame modification and cannot be added to chair later.

Q'Straint Lap Belt Model S5-6329-11. For use with WC-19 Transit Tie Down System. 24"-51" Belt Length.

O2 Holder Not compatible with Attendant Wheel Locks. Requires frame modification and cannot be added to chair later.

Order Notes			

OF-NZ-PDGBLT-01.0