



Customer and Order Information			
Purchase Order *	Tag		
Dealer/Provider Name *			
Purchaser Name and Contact Information *			
Shipping Address *			
User Information (<i>if available</i>) Weight	kgs Height	cm	* required
Base Chair			
Fuze JR 50° Pediatric Manual Tilt Wheelc	hair		\$
Frame Type & Weight Capacity			
☒ 1702025 Adjustable/Growing Width Frame 113kg/25	0 lbs Weight Capacity.		
Frame Options			
☐ 02222 Take-Apart Frame The Take-Apart frame allows atte	ndants to take the Fuze apart in seconds wi	ithout tools. pdgmobility.com/take-apart	\$
This feature reduces the weight of the heaviest piece of the Take-Apart rear crossbar is not width adjustable. PDG will p	•	, ,	
adjustable width frame (can be ordered with the chair or la	•		
Fold	Tilt	Take Take	
		apart	
FUZE TAKE-	APART Check the for more	PDG Blog	
I OZL TAKL-	for more	details.	
□ 02300 Transit Tie Down System (TTDS)			
TTDS includes 4 factory-installed transport brackets. TTDS I	nas been tested according to ANSI/RESNA W	VC 19. See Owners Manual for complete details.	
Seat Width		Overall chair width is +7.5" for 12/16" RW and +8.5" for 20/22/24" RW	
Adjustable Seat Widths			
	2"-15" Range - Set at 13"	□ 03114 12"-15" Range - Set at 14"	
□ 03115 12"-15" Range - Set at 15"		_	
□ 03215 15"-18" Range - Set at 15" □ 03216 1 □ 03218 15"-18" Range - Set at 18"	5"-18" Range - Set at 16"	03217 15"-18" Range - Set at 17"	
Seat Depth			
Standard Seat Depths (Adjustable) Output Out	4" Seat Depth	□ 04015 15" Seat Depth	
	7" Seat Depth	□ 04018 18" Seat Depth	
	·	70.1	
Frame Colour			
PDG Premium Colours View colour swatches on Pl		□ mark D. D. I	
_	ky Blue ollypop Blue	□ 05016 Poppy Red □ 05011 Lollypop Red	
OS017 Arctic Grey	· · ·	Osone Tangerine Orange	

See next page for more options >



January 1, 2024



FUZE JR

05020					05021		1.91				П	05040	D 1.1	e Gum	D: I			
_	Olive Green Leaf Green				_		ı Lilac	y Purple			_	05012 05014		ie Gum dil Yelli				
							senberr	y Purpie				05014	рапо	ali reli	ow			
05200	Custom Colour	Contact	Permobi	I for spec	cificatio	ns.												\$
Armre	ests																	
06000	No Armrests																	
	Height Adjusta	ble Arm	rests (Sinale	Post)	8"-11'	" Range.											\$
	Armrest Heig								hlank th	ne defau	lt sottin	a will b	a usad					, , , , , , , , , , , , , , , , , , ,
3	Seat Pan to top			iiiicata (WIII DC 3		_	nclude height o			iic sectiii	g will b	c uscu.					
	Locking Flip-			Not reco	mmond						ot comr	natible v	with Fol	d-down	Rack			
☐ 06308	Set at 8"	и р / п.п.						CACCISIVE SITE	ingtii oi	toric. iv	or comp	Jatibic 1	WICH I ON	a down	Duck.			\$
_	Set at 10"				_		at 11"											
Armp	a d s																	
	Regular Armp	oads																
07100	Desk Length - 2" x	10"			07101	Full I	Length	- 2" x 14"										
	Waterfall Arm	npads																\$
07105	Desk Length - 2" x	10"			07106	Full I	Length	- 2" x 14"										
	Wide Armpad	ls May ir	nterfere v				•											\$
07110	Desk Length - 3" x	10"			07111	Full I	Length	- 3" x 12"										
	Gel Armpads	May inte	rfere wit	h wheels	in som	e tilt con	nfiguratio	ons.										\$
07120	Full Length - 2" x 1	12"			07121	Full I	Length	- 3.5" x 12"										
Armre	est Option	s																
7.11111																		
07210	Armrest Wide 1" Total Additiona		love Arm	irests ou	tward b	y up to 1	ı" on eac	h side. Seat siz	ze aoes	not chai	nge.							ċ
_	2" Total Additiona																	\$ \$
— 07211	2 Total / Idaitiona	i widti																
Seat	Pan																	
08000	No Seat Pan																	
08001	Solid Aluminiu	m Seat P	an															\$
Seat	Height																	
> Don't forget	Select desired	l Seat-to	-Floor	Heigh	it st	F Height	is adjust	table.										
ioiget		5	" Caste	rs							6" Cast							
		4" 15"	16"	17"	18"	19"	20"	RW	13"	14"	15"	16"	17"	18"	19"	20"		
]]						12" 16"										
	20"							20"										
	22"							22"										
	24"							24"										
	6" Casters & 6" Forks									;	8" Cast	ers & 8	3" Forks	5				
		4" 15"	16"	17"	18"	19"	20"	RW	13"	14"	15"	16"	17"	18"	19"	20"		
		<u> </u>						12" 16"										
	20"							20"										
	22"							22"										
	24"							24"										
1																		





Caste						
Caste						
	Urethane Casters					
_		061 6" x 1.25" Caster size	☐ 11081 8" x 1.25" Caster size			
11063	6" x 1.50" Caster size			\$		
11084	8" x 2.00" Caster size			\$		
	Pneumatic Casters					
l	6" x 1.25" Caster size			\$		
_	8" x 1.25" Caster size			\$		
LI 11184	8" x 2.00" Caster size			\$		
Rear	Wheels					
П 12012	Composite Wheels 12" Wheel size	016 16" Wheel size	☐ 12020 20" Wheel size			
	22" Wheel size		Li 12020 ZO Wheel Size			
12022		024 24 Wheel Size		ė		
	Spoke Wheels		П жи ми	\$		
12120	20" Wheel size		☐ 12124 24" Wheel size			
		positioning preference. If left blank, th	_			
12401	_ · _	ding interferance with other chair func 402 Mid	tions, PDG may not be able to accommodate stated preference. 12403 Front Less stable			
12401	near More Stable	402 IVIIQ	LI 12403 FIORE LESS STADIE			
Axle	Туре					
☐ 13000	Quick Release Rear Axles					
☐ 13010	Fixed Rear Axles					
13010	rixeu neai Axies					
Rear	Tires					
☐ 14000	Urethane Tires					
		411-i-h4 1/3"44		\$		
☐ 14010 Pneumatic Tires May result in a finished Seat Height 1/2" greater than stated. ☐ 14020 Pneumatic Tires with Flat-Free Inserts May result in a finished Seat Height 1/2" greater than stated. Not available with Spoke Wheels.						
☐ 14020 F	Pneumatic Tires with Flat-Free Inserts	Nay result in a finished Seat Height 1/2	greater than stated. Not available with Spoke Wheels.	\$		
Hand	r i m s		Handrims are available only with 20", 22", and 24" Rear Whe	eels.		
☐ 15000	No Handrims					
15010				\$		
LJ 15020						
15030 Projection Handrims Composite Wheels only. 10 Projections, 30°, 1-1.8" Length.						
\A/ la = =	l l a a ka					
wnee	el Locks					
_	User Wheel Locks					
16010	Push to Lock	020 Pull to Lock				
16030	Attendant Wheel Locks (Push to Lock)	Not compatible with Wheel Lock Ext	ensions.	\$		
16005	Foot Operated Wheel Lock Rear-mounted	d unilateral single-activation lock. Com	patible with 19" and 20" STF Height only.	\$		
☐ 16300						
	12" Wheels compatible with 13", 14", 17.5", 18.5", 19.5" STF Height only. 20" Wheels compatible with 16", 17", 18" STF Height only.					
	User-activated Unilateral Wheel Lock Pull to Lock.					
16310	Left Activation	Right Activation				
\\\						
Whee	el Lock Options					
16100	Wheel Lock Extensions Not compatible w	th Attendant Wheel Lock.		\$		
۸ n + :	Tippors					
	Tippers					
17010	Rear Anti-Tippers Required Safety Option.			\$		





Back	Posts	
	Back Post Style	
□ 18100	·	
	Back Post Type	
☐ 18200	Straight	
	Back Post Height Measured from the Seat Pan to the Handle.	
□ 18420	Short (17")	
	Back Post Folding Fold-down Back is not compatible with Reclining Backrest.	
☐ 19220	Fold-down I 19221 Non-folding	
	Seat to Back Angle	
19090	Set at 90°	
19108	Set at 114°	
Back	Options	
	Angle/Height Adjustable Stroller Handle Not compatible with Headrest Mounting Plate or Cane Handle Back.	\$
19010		
19050	Removable Cane Handle Push Bar Not compatible with Stroller Handle Back.	\$
19212	Headrest Mounting Plate	\$
	Not compatible with Angle/Height Adjustable Stroller Handle, Cane Handle Back. Not required if mounting to a solid Back.	
Tilt	Activation	
	Attendant Tilt only Select trigger mounting location below.	
23011	Right Back Post 23012 Left Back Post	
23400	Power Tilt 40° tilt range. Includes 2 batteries for off-chair charging. pdgmobility.com/power-tilt	
23400		\$
Sele	instance on Egit Suc	
> Cont	trol Charlete Fac Curinels Dance Making willed	
Swit	Optional for Egg Switch: 23445 Swing Away Mounting Hardware Not compatible with all Headrest makes and models.	\$
	Specify Headrest to be used:	Į.
	Tilt Limit Optional. If no tilt limit is selected, the full tilt range will be available.	
23220	Set at 20°	
Recl		
23310		\$
	30° maximum recline. Not compatible with Cane Handle Back, Fold-down Back, Requires 23" Angle/Height Adjustable Stroller Handle with 8° Bend. Not available with 15" or 16" Seat Depth.	
	·	
Fron	t Rigging	
 25000	No Front Rigging 25001 Sector Blocks only	
	Easy-Out **Front Rigging** Effortless insertion and removal. No Hanger Bracket remains on frame. *pdgmobility.com/easy-out**	
25410	Fixed 70°	\$
☐ 25420	Universal Angle Adjustable (0°-110°) Set at angle: (use increments of 10°)	\$
	Adjust angle by loosening one bolt. Tool-free leg-length adjustment. Front Rigging can interfere with casters in the 90-110° settings.	
	Swing Away Front Rigging Legacy Design. Not compatible with Easy-Out.	
25130	Swing Away 60°	
25160	Swing Away 90° Adjustable down to 3.5" Leg Length. Includes 11"-16" Extension Tubes. Not compatible with 8" Casters.	\$
25200	Swing Away Elevating Legrests Includes Calf Pads. Not compatible with 12" or 13" Seat Width.	\$
25300	1" Offset Hangers for Swing Away	\$
 25110	Standard Plug In 70° Front Rigging Legacy Design. Not compatible with Easy-Out.	





[o o t		
	plates	
26010	Composite Footplates Not available on 12" Seat Width.	
26020	Aluminium Angle Adjustable Footplates	\$
26030	One Piece Fixed Footplate Available on Plug In Front Rigging only. Requires selection of Composite or Aluminium Angle Adjustable.	\$
26040	One Piece Flip-up Footplate Requires selection of Composite or Aluminium Angle Adjustable.	\$
26050	Interlocking Angle Adjustable Footplates	\$
Foot	rest/Legrest Accessories	
	Calf Pad Not compatible with Gel Padding.	
<u> </u>	For Easy-Out TM Front Rigging Includes reinforced premium Calf Pad mount.	\$
27010	For Swing Away Front Rigging	\$
27020	Gel Padding Not compatible with Calf Pad or Easy-Out Front Rigging.	\$
	Gel Knee Pad	
□ 27032	For Easy-Out [™] Angle Adjustable Front Rigging	\$
27030	For Swing Away ELR Front Rigging	\$
27040	Length Adjustable Heel Loops	\$
27050	Bodypoint Padded Calf Strap	\$
Front	Rigging Extension Tubes	
	Regular Extension Tubes No selection required for 90° Front Rigging.	
28010	Short 14"-18" for Easy-Out Front Rigging 13"-17" for Swing Away and Standard Plug In Front Rigging	
28020	Long 18"-24" for Easy-Out Front Rigging 15"-19" for Swing Away and Standard Plug In Front Rigging	\$
1	Lower Leg Length If provided, Front Rigging will be set to this length by PDG. If left blank, the default setting will be used.	
7	Seat Pan to Foot Plates: Measured along the length of the Front Rigging. Consider the height of your Seat Cushion.	
Misce	ellaneous Options	
	Spoke Guards Available for 20"-24" Composite Rear Wheels. Made from durable and lightweight aluminium.	\$
30020	Black 30021 Frame Colour	
_	Stealth Flip Down Abductor Requires Solid Seat Pan.	\$
30060	Small Pad 3"x4"x3"x2" size	
30090	Hip Belt Mount Provides improved mounting options for Bodypoint Hip Belt or other third-party belts.	\$
30160	Clear Lap Tray (Slide On) Available for Seat Widths of 17"-18" only. Not compatible with Contour Arm Trough.	\$
30200	Q'Straint Lap Belt Model S5-6329-11. For use with WC-19 Transit Tie Down System. 24"-51" Belt Length.	\$
30222	Wheelchair Backpack Black with PDG Logo. 17"x14" size.	\$
30170	Adhesive Back Hook Strip, 2" x 30" For Cushion mounting.	\$
Orde	r Notes	

OF-NZ-PDGFJR-01.0