



Customer and Order Information					
Purchase Order *	Тад				
Dealer/Provider Name *					
Purchaser Name and Contact Information *					
Shipping Address *					
User Information <i>(if available)</i> Weight	_kgs Height cm	* required			

Order Notes/Instructions

Base Chair

	Fuze M50 50° Manual Tilt Wheelchair with Mid-Wheel Drive				
×	FUZE-M5	⁰ Fuze 50° Manual Tilt Wheelchair Includes articulating rear casters and places drive wheels in the middle of the chair at the centre of gravity.	\$		
F	r a m e	e Type & Weight Capacity			
		Fixed Width Frame Select a Fixed Seat Width below.			
	02010	136kg/300 lbs Weight Capacity			
	02011	481kg/400 lbs Weight Capacity Not compatible with Transit Tie Down System. Requires Flat-free Tyres or Heavy Duty Spoke Drive Wheels.			
	02025	Adjustable Width Frame 113kg/250 lbs Weight Capacity. Select an Adjustable Seat Width	\$		
	below.				

Frame Options

□ 02300 Transit Tie Down System (TTDS)

TTDS includes 4 factory-installed transport brackets. TTDS has been tested according to ANSI/RESNA WC 19. See Owners Manual for complete details.
Tested to max. Weight Capacity of 136kg/300 lbs.

Seat	Width				Overall chair width is +8.5".	
	Fixed Seat Widths Or	der with Fixed Frame.				
03015	15" Seat Width	03016	16" Seat Width	03017	17" Seat Width	
03018	18" Seat Width	03019	19" Seat Width			
03020	20" Seat Width	03021	21" Seat Width	03022	22" Seat Width	
03023	23" Seat Width					\$
03024	24" Seat Width					\$
	Adjustable Seat Width	S Order with Adjustabl	e Frame.			
03215	15"-19" Range - Set at 15"	03216	15"-19" Range - Set at 16"	03217	15"-19" Range - Set at 17"	
03218	15"-19" Range - Set at 18"	03219	15"-19" Range - Set at 19"			
c .						
Seat	Depth					
	Standard Seat Depths	(Adjustable)				
04015	15" Seat Depth	04016	16" Seat Depth	04017	17" Seat Depth	
04018	18" Seat Depth	04019	19" Seat Depth			
04020	20" Seat Depth					
	Custom Seat Depths	Requires Stroller Handle	Back - Straight. Not compatible with	n Reclining or Fold-dowr	n Back.	
04021	21" Seat Depth					\$
04022	22" Seat Depth					s

Frame Colour					
	PDG Premium Colours View colour swatches on PDG's website. pdg	mobility.com/colours			
05001	Black Shimmer 🛛 05015 Sky Blue	05016 Poppy Red			
05003	Fine Texture Black 🛛 05010 Lollypop Blue	05011 Lollypop Red			
05017	Arctic Grey Doto 05018 Tropical Teal	05019 Tangerine Orange			
05020	Olive Green Dive Green Dive Green	D 05012 Bubble Gum Pink			
05022	Leaf Green 🛛 05023 Boysenberry Purple	05014 Daffodil Yellow			
05200	Custom Colour Contact Permobil for specifications.	\$			
A r m r	octs				
	No Armrests	<u>^</u>			
	Height Adjustable Armrests (Single Post)	\$			
06114	10"-14" Range 🗌 06116 12"-16" Range				
06100	Fixed Height Armrests (12") Full Length Armpad only.				
1	Armrest Height If provided, Armrests will be set to this height by PDG. If left				
7	Seat Pan to top of Armrest: Does not include height	of Armpad			
1	Armrest Position Indicate preference for Armrest position. If left blank, the	-			
06401	In the interest of maintaining chair stabily and avoiding interferance with other chair Rear Default Position Default Position Rear	r functions, PDG may not be able to accommodate stated preference.			
00401		• • • • • • • • • • • • • • • • • • •			
	Locking Flip-up Armrests Not recommended for users with excessive st Not compatible with Fold-down Back. Only available with Regular Full Length and D				
06310	Set at 10" 06311 Set at 11"	D 06312 Set at 12"			
06313	Set at 13" 06314 Set at 14"				
Armp	o a d s				
	Regular Armpads				
07100	Desk Length - 2" x 10" 🛛 07101 Full Length - 2" x 14"				
	Waterfall Armpads	\$			
07105	Desk Length - 2" x 10" 🛛 07106 Full Length - 2" x 14"				
	Wide Armpads May interfere with wheels in some tilt configurations.	\$			
07110	Desk Length - 3" x 10" 🛛 07111 Full Length - 3" x 12"				
	Gel Armpads May interfere with wheels in some tilt configurations.	\$			
07120	Full Length - 2" x 12" Image: 07121 Full Length - 3.5" x 12"				
A					
	est Options				
07210	Armrest Wideners Move Armrests outward by 0.5" on each side for 1" total and	dditional width. Seat size does not change. \$			
Seat	Pan				
08000	No Seat Pan				
_		ć			
08001	Solid Aluminium Seat Pan	\$			
Seat	Height				
🔪 Don't		he range of the chosen Axle Plate (Low/Standard). RC refers to the size of the Rear Casters.			
forget	Chairs with Swing-Away Front Rigging are set up with up to 5° of pre-tilt to avoid int				
	to 1" compared to the selected value. Easy-Out is not affected.				
	5" Front Casters RW 13" 14" 15" 16" 17" 18" 19" 20" RC	6" Front Casters & 6" Forks RW 13" 14" 15" 16" 17" 18" 19" 20" RC			
	20" I II III III IIII IIIII IIIIIIIIIIIIIIIIIIIIIIIIIIIIIIIIIIII	NW 13 14 13 16 17 18 19 20 NC 20" □ □ □ □ □ 5"			
	22"	22"			
	24" Low STF 6"	24" Low STF 🔲 🔲 🔲 🌀 6"			
	6" Front Casters & 8" Forks	6" Front Casters & Frog Legs Suspension Forks			
	RW 13" 14" 15" 16" 17" 18" 19" 20" RC	RW 13" 14" 15" 16" 17" 18" 19" 20" RC			
	20"	20" 🗌 🔲 🔲 5"			
	22"	22"			
	24" Low STF 🔲 🔲 🔲 🔲 🌀 6"	24" Low STF 🔲 🗖 🌀 6"			

Front Casters					
	Urethane Casters Select Front Caster size here. Rear Caster size as per STF tables.				
11051	5" x 1.25" Caster size	11061	6" x 1.25" Caster siz	e	
11063	6" x 1.50" Caster size				\$
11260	Soft-Roll Casters 6" x 1.50" C	aster size. Urethane t	ire & Silver Anodized Alι	uminium hub. Available as Front Casters only.	\$
11400	Frog Legs Suspension Fork	S Requires 6" x 1.5	0" Soft-Roll Casters. Sus	pension Forks used for Front Casters only.	\$
Drive	e Wheels				
12020	Composite Wheels 20" Wheel size		22" Wheel size	12024 24" Wheel size	
12020	Spoke Wheels	L 12022	22 Wheel Size		\$
□ 12120	20" Wheel size	□ 12122	22" Wheel size	□ 12124 24 " Wheel size	Ş
	24" Heavy Duty Spoke Whe		22 Wheel Size		\$
L 12224	24 Heavy Duty Spoke wile	:015			Ļ
Axle	Туре				
13000	Quick Release Drive Wheel	Axles			
13010	Fixed Drive Wheel Axles				
Drive	e Wheel Tires				
14000	Urethane Tires				
14010	Pneumatic Tires May result	in a finished Seat Hei	ght 1/2" greater than sta	ited.	\$
14020	Pneumatic Tires with Flat-Fre	e Inserts May r	esult in a finished Seat H	leight 1/2 [~] greater than stated. Not available with Spoke Wheels.	\$
Hand	lrims				
15000	No Handrims				
15010	Standard Aluminium Hand	rims			
15020	Plastic Coated Handrims				\$
15030	Projection Handrims Comp	oosite Wheels only. 1	0 Projections, 30°, 1-1.8"	Length.	\$
Whee	el Locks				
	User Wheel Locks				
□ 16010	Push to Lock	16020	Pull to Lock		
	User-activated Unilateral			to 22" Seat Width only	\$
16310	Left Activation	16311			•
Į					
Whee	el Lock Options				
16100	Wheel Lock Extensions				\$
Pack	Posts				
DACK					
	Back Post Style	_			
18100	Stroller Handle Back	18105	Cane Handle Back	Not compatible with Headrest Mounting Plate.	
	Back Post Type				
L 18200	Straight		8° Bend		
	-	ed from the Seat Pan f			
18420	Short (17")		Tall (23")		
☐ 19220	-		batible with Reclining Ba	ckrest.	
19220	Fold-down	19221	Non-folding		
19090	Seat to Back Angle	19096	Set at 98°	□ 19102 Set at 106°	
L 19090	Set at 90				
19108	Set at 114°	19114	Set at 122°		

Back	Options				
	Angle/Height Adjustable Stroller Handle Not compatible with Headrest Mounting Plate or Cane Handle Back.	\$			
19010	Button on Outside 🗌 2819011 Button on Inside				
	Endomorph Back Backrest will be narrower than Seat by total of 2x the Offset selected below. Minimum width of Backrest is 12".	\$			
18102	Not compatible with Flip-up Armrests, Reclining Backrest. 1" Offset per side 15118103 1.5" Offset per side 2818104 2" Offset per side				
19212		\$			
	Upholstery				
20000	No Back Upholstery				
	Standard Upholstery Not available with Cane Handle Back.	\$			
20418					
20450		\$			
	Position of Upholstery Select the desired position of the top of the Upholstery relative to the Seat Pan.				
	Style 17" 18" 19" 20" 21" 22" 23" 24" 25" Style 17" 18" 19" 20" 21" 22" 23"	24" 25"			
	Short I <td></td>				
	Regular 🗌 🔲 🗖				
	Tension Adj				
Tilt	Activation				
	Attendant Tilt only Select trigger mounting location below.				
D 23011					
	Tilt Limit Optional. If no tilt limit is selected, the full tilt range will be available.				
□ 23220	Set at 20° Image: 23230 Set at 30° Image: Image: 23240 Set at 40°				
Tip	Configuration (Front Caster Lift)				
	Attendant Tip only Select trigger mounting location below.				
23451					
	Tip Clearance Limit (Front Caster Lift) Actual tip may vary by up to 0.5". No selection required if Trigger is omitted.				
D 23455	_				
Recli	in e				
23310		\$			
L 23310	Reclining Backrest (Manual) 30° maximum recline. Not compatible with Cane Handle Back, Fold-down Back. Not available with 21" & 22" Seat Depth.	Ş			
Finished Back Post Height is 3" taller than selected Back Post Height.					
Fron	t Rigging				
25000	No Front Rigging 🛛 25001 Sector Blocks only				
	Easy-Out Front Rigging Effortless insertion and removal. No Hanger Bracket remains on frame. pdgmobility.com/easy-out				
25410	Fixed 70°	\$			
25420		\$			
	Adjust angle by loosening one bolt. Tool-free leg-length adjustment. Front Rigging can interfere with casters in the 90-110° settings. Optional for Universal AA:				
	Swing Away Front Rigging Legacy Design. Not compatible with Easy-Out, Push to Lock Wheel Locks. Requires pre-tilt of up to 5°.				
D 25130					
□ 25200		\$			
E o o t					
	plates Comparis Footplates				
26010 26020		ć			
_	······································	\$			
_		\$			
□ 26050	Interlocking Angle Adjustable Footplates Available for Seat Widths up to 21" only.	\$			

Foot	rest/Legrest Accessories				
	Calf Pad Not compatible with Gel Padding.				
D 27012	For Easy-Out Front Rigging Includes reinforced premium Calf Pad mount. Requires pre-tilt of up to 5°.	\$			
D 27010	For Swing Away Front Rigging	\$			
27020	Gel Padding Not compatible with Calf Pad or Easy-Out Front Rigging.	\$			
	Gel Knee Pad				
27032	For Easy-Out Angle Adjustable Front Rigging	\$			
D 27030	For Swing Away ELR Front Rigging	\$			
27040	Length Adjustable Heel Loops	\$			
27050	Bodypoint Padded Calf Strap Sizes greater than 22" are not padded.	\$			
Front	Rigging Extension Tubes				
	Regular Extension Tubes No selection required for Easy-Out AA High-mount Option.				
28010	Short <u>14"-18"</u> for Easy-Out Front Rigging <u>13"-17"</u> for Swing Away Front Rigging				
28020	Long <u>18"-24"</u> for Easy-Out Front Rigging <u>15"-19"</u> for Swing Away Front Rigging	\$			
	💪 Lower Leg Length If provided, Front Rigging will be set to this length by PDG. If left blank, the default setting will be used.				
-	Seat Pan to Foot Plates: Measured along the length of the Front Rigging. Consider the height of your Seat Cushion.				
Misc	ellaneous Options				
	Spoke Guards Available for 20"-24" Composite Drive Wheels. Made from durable and lightweight aluminium.	\$			
30020	Black 🛛 30021 Frame Colour				
	Stealth Flip Down Abductor Includes wedge-style pad. Requires Solid Seat Pan.	\$			
30060	Small Pad 3"x4"x3"x2" size 🛛 30062 Large Pad 5"x5"x4"x3" size				
30080	Gel Hip Guides Reduces available Seat Width by 2".	\$			

Hip Belt Mount Provides improved mounting options for Bodypoint Hip Belt or other third-party belts.

Q'Straint **Lap Belt** Model S5-6329-11. For use with WC-19 Transit Tie Down System. 24"-51" Belt Length.

Clear Lap Tray (Slide On) Available for Seat Widths of 17"-22" only. Will interfere with Drive Wheel when in tilt.

Ventilator Bracket Compatible with LTV1 (laptop) ventilator.

Medical Necessities Backpack Black with Permobil Logo.

Adhesive Back Hook Strip, 2" x 30" For Cushion mounting.

30090

30152

30160

30200

30222

30170

Order Notes

\$

\$

\$

\$

\$

\$