


Customer and Order Information		
Purchase Order *	Tag	v.0401
Dealer/Provider Name *		
Purchaser Name and Contact Information *		
Shipping Address *		
User Information (if available)	Weight _____ kgs	Height _____ cm *required

Base Chair	
Fuze T50n 50° Manual Tilt Wheelchair	
<input checked="" type="checkbox"/> FUZE-T50N	Fuze T50n 50° Manual Tilt Wheelchair Reduces overall chair width to seat width plus only 4". \$

Frame Type & Weight Capacity	
Fixed Width Frame Select a Fixed Seat Width below.	
<input type="checkbox"/> 02010	136kg/300 lbs Weight Capacity
<input type="checkbox"/> 02011	181kg/400 lbs Weight Capacity Not compatible with Transit Tie Down System.
<input type="checkbox"/> 02025	Adjustable Width Frame 113kg/250 lbs Weight Capacity. Select an Adjustable Seat Width below. \$

Frame Options	
<input type="checkbox"/> 02222	Take-Apart Frame The Take-Apart frame allows attendants to take the Fuze apart in seconds without tools. pdgmobility.com/take-apart \$ This feature reduces the weight of the heaviest piece of the wheelchair to 13kg/29 lbs or less. Perfect for transporting it in the boot of a car or SUV. Not compatible with Power Tilt, Drum Brakes, Ventilator Tray, Ventilator Battery Tray, DRB, User Wheel Locks. Take-Apart rear crossbar is not width adjustable. PDG will provide one no-charge crossbar in a different width over the lifetime of each chair ordered with adjustable width frame (can be ordered with the chair or later). Note: Crossbar for the T50n is 4" shorter than the Seat Width.
	
<input type="checkbox"/> 02300	Transit Tie Down System (TTDS) TTDS includes 4 factory-installed transport brackets. TTDS has been tested according to ANSI/RESNA WC 19. See Owners Manual for complete details. Tested to max. Weight Capacity of 136kg/300 lbs.

Seat Width		Overall chair width is +4.0" for 12" RW
Fixed Seat Widths Order with Fixed Frame.		
<input type="checkbox"/> 03016	16" Seat Width	
<input type="checkbox"/> 03017	17" Seat Width	
<input type="checkbox"/> 03018	18" Seat Width	
<input type="checkbox"/> 03019	19" Seat Width	
<input type="checkbox"/> 03020	20" Seat Width	\$
<input type="checkbox"/> 03021	21" Seat Width	\$
<input type="checkbox"/> 03022	22" Seat Width	\$
<input type="checkbox"/> 03023	23" Seat Width	\$
<input type="checkbox"/> 03024	24" Seat Width	\$
Adjustable Seat Widths Order with Adjustable Frame.		
<input type="checkbox"/> 03216	16"-19" Range - Set at 16"	
<input type="checkbox"/> 03217	16"-19" Range - Set at 17"	
<input type="checkbox"/> 03218	16"-19" Range - Set at 18"	
<input type="checkbox"/> 03219	16"-19" Range - Set at 19"	
<input type="checkbox"/> 03319	19"-20" Range - Set at 19"	
<input type="checkbox"/> 03320	19"-20" Range - Set at 20"	\$

Seat Depth

Standard Seat Depths (Adjustable)

- | | | |
|---|---|---|
| <input type="checkbox"/> 04015 15" Seat Depth | <input type="checkbox"/> 04016 16" Seat Depth | <input type="checkbox"/> 04017 17" Seat Depth |
| <input type="checkbox"/> 04018 18" Seat Depth | <input type="checkbox"/> 04019 19" Seat Depth | |
| <input type="checkbox"/> 04020 20" Seat Depth | | |

\$

Custom Seat Depths

Requires Stroller Handle Back - Straight. Not compatible with Reclining or Fold-down Back.

- | |
|---|
| <input type="checkbox"/> 04021 21" Seat Depth |
| <input type="checkbox"/> 04022 22" Seat Depth |

\$

\$

Frame Colour

PDG Premium Colours

View color swatches on PDG's website. pdgmobility.com/colors

- | | | |
|---|---|---|
| <input type="checkbox"/> 05001 Black Shimmer | <input type="checkbox"/> 05015 Sky Blue | <input type="checkbox"/> 05016 Poppy Red |
| <input type="checkbox"/> 05003 Fine Texture Black | <input type="checkbox"/> 05010 Lollypop Blue | <input type="checkbox"/> 05011 Lollypop Red |
| <input type="checkbox"/> 05017 Arctic Grey | <input type="checkbox"/> 05018 Tropical Teal | <input type="checkbox"/> 05019 Tangerine Orange |
| <input type="checkbox"/> 05020 Olive Green | <input type="checkbox"/> 05021 Lush Lilac | <input type="checkbox"/> 05012 Bubble Gum Pink |
| <input type="checkbox"/> 05022 Leaf Green | <input type="checkbox"/> 05023 Boysenberry Purple | <input type="checkbox"/> 05014 Daffodil Yellow |

- | |
|--|
| <input type="checkbox"/> 05200 Custom Colour Contact Permobil for specifications. |
|--|

\$

Armrests

- | |
|---|
| <input type="checkbox"/> 06000 No Armrests |
|---|

Height Adjustable Armrests (Single Post)

\$

- | | |
|--|--|
| <input type="checkbox"/> 06114 10"-14" Range | <input type="checkbox"/> 06116 12"-16" Range |
|--|--|

- | |
|--|
| <input type="checkbox"/> 06100 Fixed Height Armrests (12") Full Length Armpad only. |
|--|



Armrest Height

If provided, Armrests will be set to this height by PDG. If left blank, the default setting will be used.

Seat Pan to top of Armrest: _____ Does not include height of Armpad



Armrest Position

Indicate preference for Armrest position. If left blank, the default setting will be used.

In the interest of maintaining chair stability and avoiding interference with other chair functions, PDG may not be able to accommodate stated preference.

- | | |
|------------------------------------|--------------------------------------|
| <input type="checkbox"/> 06402 Mid | <input type="checkbox"/> 06403 Front |
|------------------------------------|--------------------------------------|

Locking Flip-up Armrests

Not recommended for users with excessive strength or tone. Not compatible with Fold-down Back.

\$

- | | | |
|---|---|---|
| <input type="checkbox"/> 06310 Set at 10" | <input type="checkbox"/> 06311 Set at 11" | <input type="checkbox"/> 06312 Set at 12" |
| <input type="checkbox"/> 06313 Set at 13" | <input type="checkbox"/> 06314 Set at 14" | |

Armpads

Regular Armpads

- | | |
|---|---|
| <input type="checkbox"/> 07100 Desk Length - 2" x 10" | <input type="checkbox"/> 07101 Full Length - 2" x 14" |
|---|---|

Waterfall Armpads

\$

- | | |
|---|---|
| <input type="checkbox"/> 07105 Desk Length - 2" x 10" | <input type="checkbox"/> 07106 Full Length - 2" x 14" |
|---|---|

Wide Armpads

May interfere with wheels in some tilt configurations.

\$

- | | |
|---|---|
| <input type="checkbox"/> 07110 Desk Length - 3" x 10" | <input type="checkbox"/> 07111 Full Length - 3" x 12" |
|---|---|

Gel Armpads

May interfere with wheels in some tilt configurations.

\$

- | | |
|---|---|
| <input type="checkbox"/> 07120 Full Length - 2" x 12" | <input type="checkbox"/> 07121 Full Length - 3.5" x 12" |
|---|---|

Contour Arm Trough with Hand Pad

\$

Not compatible with Lap Tray, Locking Flip-up Armrests. May interfere with wheels in some tilt configurations.

- | | |
|---|--|
| <input type="checkbox"/> 07130 Right (4.5" x 18") | <input type="checkbox"/> 07131 Left (4.5" x 18") |
|---|--|

Armrest Options

Armrest Wideners

Move Armrests outward by up to 1" on each side. Seat size does not change.

- | |
|--|
| <input type="checkbox"/> 07210 1" Total Additional Width |
| <input type="checkbox"/> 07211 2" Total Additional Width |

\$

\$

Seat Pan

- 08000 **No Seat Pan**
- 08001 **Solid Aluminium Seat Pan** \$

Seat Height

➤ Don't forget **Select desired Seat-to-Floor Height** STF Height is adjustable.

12" Rear Wheels					
Caster size	16"	17"	18"	19"	20"
5"	<input type="checkbox"/>	<input type="checkbox"/>			
6"	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	
8"	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>
6" Soft Roll	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>		

Casters

- Urethane Casters**
- 11051 5" x 1.25" Caster size 11061 6" x 1.25" Caster size 11081 8" x 1.25" Caster size \$
 - 11063 6" x 1.50" Caster size \$
 - 11084 8" x 2.00" Caster size \$
- Pneumatic Casters**
- 11161 6" x 1.25" Caster size \$
 - 11181 8" x 1.25" Caster size \$
 - 11184 8" x 2.00" Caster size \$
 - 11260 **Frog Legs 6" x 1.50" Aluminium Soft-Roll Casters** \$

Rear Wheels

- 12012 **12" Composite Wheels**
- Rear Wheel Position** Indicate Rear Wheel positioning preference. If left blank, the default setting will be used.
In the interest of maintaining chair stability and avoiding interference with other chair functions, PDG may not be able to accommodate stated preference.
- 12401 Rear More stable 12402 Mid 12403 Front Less stable

Axle Type

- 13000 **Quick Release Rear Axles**
- 13010 **Fixed Rear Axles**

Rear Tires

- 14000 **Urethane Tires**
- 14010 **Pneumatic Tires** May result in a finished Seat Height 1/2" greater than stated. \$
- 14020 **Pneumatic Tires with Flat-Free Inserts** May result in a finished Seat Height 1/2" greater than stated. \$

Handrims

- 15000 **No Handrims**

Wheel Locks & Brakes

- User Wheel Locks** Not compatible with Take-Apart Frame. \$
- 16010 Push to Lock 16020 Pull to Lock
 - 16030 **Attendant Wheel Locks (Push to Lock)**
 - 16005 **Foot Operated Wheel Lock** Rear-mounted unilateral single-activation lock. Not compatible with Ventilator Tray. \$
 - 16300 **Drum Brakes** Available with Urethane Tires only. Compatible with 17.5", 18.5", 19.5" STF Height only. \$
 - User-activated Unilateral Wheel Lock** Pull to Lock. Available up to 22" Seat Width only. \$
 - 16310 Left Activation 16311 Right Activation



FUZE T50n

Wheel Lock Options

16100 **Wheel Lock Extensions** \$

Anti-Tippers

17010 **Rear Anti-Tippers** Required Safety Option. \$

Back Posts

Back Post Style

18100 Stroller Handle Back 18105 Cane Handle Back Not compatible with Headrest Mounting Plate.

Back Post Type

18200 Straight 18205 8° Bend

Back Post Height Measured from the Seat Pan to the Handle.

18420 Short (17") 18425 Tall (23")

Back Post Folding Fold-down Back is not compatible with Dynamic Rocker Back Interface, Reclining Backrest.

19220 Fold-down 19221 Non-folding

Seat to Back Angle

19090 Set at 90° 19096 Set at 98° 19102 Set at 106°

19108 Set at 114° 19114 Set at 122°

Back Options

Angle/Height Adjustable Stroller Handle Not compatible with Headrest Mounting Plate or Cane Handle Back. \$

19010 Button on Outside 19011 Button on Inside

19050 **Removable Cane Handle Push Bar** Not compatible with Stroller Handle Back. \$

Endomorph Back Backrest will be narrower than Seat by total of 2x the Offset selected below. Minimum width of Backrest is 12". \$

18102 1" Offset per side 18103 1.5" Offset per side 18104 2" Offset per side

19212 **Headrest Mounting Plate** Not compatible with Angle/Height Adjustable Stroller Handle, Cane Handle Back. Not required if mounting to a solid Back. \$

19240 **Seating Dynamics Dynamic Rocker Back Interface** \$

Not compatible with Take-Apart Frame, Fold-down Back, 30° Recline, Standard Upholstery. Only available with Stroller Handle - 8° Bend. Finished Back Post Height is 7" taller than selected Back Post Height. Maximum compatible Seat Depth is 20". 90° and 98° Seat Angle only.

Back Upholstery

20000 **No Back Upholstery**

Standard Upholstery Not available with Cane Handle Back. \$

20418 Short (18" Height) 20421 Regular (21" Height)

20450 **Tension Adjustable Upholstery** Height of Upholstery is 16". Not available with Cane Handle Back. \$

Position of Upholstery Select the desired position of the top of the Upholstery relative to the Seat Pan.

17" Back Post									
Style	17"	18"	19"	20"	21"	22"	23"	24"	25"
Short	<input type="checkbox"/>								

23" Back Post									
Style	17"	18"	19"	20"	21"	22"	23"	24"	25"
Short	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>
Regular					<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>
Tension Adj				<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>

Tilt Activation

Attendant Tilt only Select trigger mounting location below.

23011 Right Back Post 23012 Left Back Post

See next page for more options >



FUZE T50n

Power Tilt 40° tilt range. Includes 2 batteries for off-chair charging. pdgmobility.com/power-tilt

<input type="checkbox"/>	23400	Standard Power Tilt (113kg/250 lbs Weight Capacity)			\$
<input type="checkbox"/>	23401	Standard Power Tilt (159kg/350 lbs Weight Capacity)	Requires Fixed Frame.		\$
<input type="checkbox"/>	23410	Power Tilt with Manual Tilt Override (113kg/250 lbs Weight Capacity)	Allows for instant manual release of tilt in case of power tilt failure.		\$
<input type="checkbox"/>	23411	Power Tilt with Manual Tilt Override (159kg/350 lbs Weight Capacity)	Allows for instant manual release of tilt in case of power tilt failure. Requires Fixed Frame.		\$

Select Control Switch	Toggle Switch	<input type="checkbox"/>	23421	Installed on Right side	<input type="checkbox"/>	23422	Installed on Left side
	Button Switch	<input type="checkbox"/>	23431	Installed on Right side	<input type="checkbox"/>	23432	Installed on Left side
	Stealth Egg Switch	<input type="checkbox"/>	23440	Not installed			
	Optional for Egg Switch:	<input type="checkbox"/>	23445	Swing Away Mounting Hardware	Not compatible with all Headrest makes and models.		\$

Specify Headrest to be used: _____

Tilt Limit Optional. If no tilt limit is selected, the full tilt range will be available.

<input type="checkbox"/>	23220	Set at 20°	<input type="checkbox"/>	23230	Set at 30°	<input type="checkbox"/>	23240	Set at 40°
--------------------------	-------	------------	--------------------------	-------	------------	--------------------------	-------	------------

Recline

<input type="checkbox"/>	23310	Reclining Backrest (Manual)		\$
--------------------------	-------	------------------------------------	--	----

30° maximum recline. Not compatible with Cane Handle Back, Fold-down Back. Not available with 22" Seat Depth. Finished Back Post Height is 3" taller than selected Back Post Height.

Front Rigging

<input type="checkbox"/>	25000	No Front Rigging	<input type="checkbox"/>	25001	Sector Blocks only
--------------------------	-------	-------------------------	--------------------------	-------	---------------------------

Easy-Out™ Front Rigging Effortless insertion and removal. No Hanger Bracket remains on frame. pdgmobility.com/easy-out

<input type="checkbox"/>	25410	Fixed 70°		\$
<input type="checkbox"/>	25420	Universal Angle Adjustable (0°-110°)	Set at angle: _____ (use increments of 10°)	\$

Adjust angle by loosening one bolt. Tool-free leg-length adjustment. Front Rigging can interfere with casters in the 90-110° settings.

Swing Away Front Rigging Legacy Design. Not compatible with Easy-Out. Requires pre-tilt of 5°.

<input type="checkbox"/>	25130	Swing Away 60°	<input type="checkbox"/>	25140	Swing Away 70°
<input type="checkbox"/>	25160	Swing Away 90°	Includes 11"-16" Extension Tubes. Not compatible with 8" Casters.		\$
<input type="checkbox"/>	25200	Swing Away Elevating Legrests	Includes Calf Pads.		\$
<input type="checkbox"/>	25300	1" Offset Hangers for Swing Away		\$	
<input type="checkbox"/>	25110	Standard Plug In 70° Front Rigging	Legacy Design. Not compatible with Easy-Out.		\$

Footplates

<input type="checkbox"/>	26010	Composite Footplates		\$
<input type="checkbox"/>	26020	Aluminium Angle Adjustable Footplates		\$
<input type="checkbox"/>	26030	One Piece Fixed Footplate	Available on Plug In Front Rigging only. Requires selection of Composite or Aluminium Angle Adjustable.	\$
<input type="checkbox"/>	26040	One Piece Flip-up Footplate	Requires selection of Composite or Aluminium Angle Adjustable.	\$
<input type="checkbox"/>	26050	Interlocking Angle Adjustable Footplates	Available for Seat Widths up to 21" only.	\$

Footrest/Legrest Accessories

Calf Pad Not compatible with Gel Padding.

<input type="checkbox"/>	27012	For Easy-Out™ Front Rigging	Includes reinforced premium Calf Pad mount.	\$
<input type="checkbox"/>	27010	For Swing Away Front Rigging		\$
<input type="checkbox"/>	27020	Gel Padding	Not compatible with Calf Pad or Easy-Out Front Rigging.	\$

Gel Knee Pad

<input type="checkbox"/>	27032	For Easy-Out™ Angle Adjustable Front Rigging		\$
<input type="checkbox"/>	27030	For Swing Away ELR Front Rigging		\$
<input type="checkbox"/>	27040	Length Adjustable Heel Loops		\$
<input type="checkbox"/>	27050	Bodypoint Padded Calf Strap	Sizes greater than 22" are not padded.	\$



FUZE T50n

Front Rigging Extension Tubes

Regular Extension Tubes No selection required for 90° Front Rigging

- 28010 Short 14"-18" for Easy-Out Front Rigging 13"-17" for Swing Away and Standard Plug In Front Rigging
- 28020 Long 18"-24" for Easy-Out Front Rigging 15"-19" for Swing Away and Standard Plug In Front Rigging

\$



Lower Leg Length If provided, Front Rigging will be set to this length by PDG. If left blank, the default setting will be used.

Seat Pan to Foot Plates: _____ Measured along the length of the Front Rigging. Consider the height of your Seat Cushion.

Miscellaneous Options

Stealth Flip Down Abductor Requires Solid Seat Pan.

\$

- 30060 Small Pad 3"x4"x3"x2" size 30062 Large Pad 5"x5"x4"x3" size

30070 QR Bracket - Accessory Mount

\$

30080 Gel Hip Guides Reduces available Seat Width by 2".

\$

30090 Hip Belt Mount Provides improved mounting options for Bodypoint Hip Belt or other third-party belts.

\$

30150 Ventilator Tray Reduces ground clearance. Chair may be unstable when unoccupied. Minimum Seat Width is 20". Not compatible with Power Tilt, Foot Operated Wheel Locks.

\$

30152 Ventilator Bracket Compatible with LTV1 (laptop) ventilator.

\$

30160 Clear Lap Tray (Slide On) Available for Seat Widths of 17"-22" only. Not compatible with Contour Arm Trough.

\$

30200 Q'Strain Lap Belt Model S5-6329-11. For use with WC-19 Transit Tie Down System. 24"-51" Belt Length.

\$

30222 Wheelchair Backpack Black with PDG Logo. 17"x14" size.

\$

30170 Adhesive Back Hook Strip, 2" x 30" For Cushion mounting.

\$

Order Notes