## **PDG BENTLEY LT**

Custo	mer and Order Information				
Purchase	· Order *	Tag			
Dealer/P	rovider Name *				
Purchase	r Name and Contact Information *				
Shipping	Address *				
	rmation (if available) Weight	kg Height	cm		* required
O " ol o "	Notes / Instructions				
Order	Notes/Instructions				
Base	Chair				
	Bentley LT 20° Manual Tilt Wheelchair				
BENTLEY-	LT Bentley LT 20° Manual Tilt Wheelchair Aluminium Frame is not recommended for agitated to	isers.			\$
<u>(i)</u>	Choose the standard <b>Bentley</b> with a steel fra		See senarate	order form	
	·	e ror agreece or ricarier abers.	see separate	order rooms	
Frame	Type & Weight Capacity				
	Frame Type All frames offer 136kg/300 lbs Weight	Capacity.			
2402010	Fixed Width Frame Select a Fixed Seat Width below				
2402025	Adjustable Width Frame Select an Adjustable Seat	Width below.			\$
	User Weight Range Required for setup of tilt up	lift force.			
2402430	Up to 34kg/75 lbs	34kg/75 lbs to 45kg/100 lbs	2402432	45kg/100 lbs to 52kg/115 lbs	
2402433	52kg/115 lbs to 68kg/150 lbs	68kg/150 lbs to 90kg/200 lbs	2402435	90kg/200 lbs to 113kg/250 lbs	
2402436	113kg/250 lbs to 136kg/300 lbs				
Frame	Options				
2402300	Transit Tie Down System (TTDS)				
	TTDS includes 4 factory-installed transport brackets. TTD	S has been tested according to ANSI/RESN	IA WC 19. See Ov	vners Manual for complete details.	
Seat \	Width	Overall chair width is +9.5" with	12/16" Rear Whe	els and +10.5" with 20/22/24" Rear Wheels.	
	Fixed Seat Widths Order with Fixed Frame.				
2403015	15" Seat Width 2403016	16" Seat Width	☐ 2403017	17" Seat Width	
2403018	18" Seat Width	19" Seat Width	_		
2403020	_	21" Seat Width	2403022	22" Seat Width	\$
2403023	23" Seat Width				\$
2403024	24" Seat Width				\$
	Adjustable Seat Widths Order with Adjustable	e Frame.			
2403112	<u> </u>	12"-16" Range - Set at 13"	2403114	12"-16" Range - Set at 14"	
2403115	12"-16" Range - Set at 15" 2403116	12"-16" Range - Set at 16"			
7403215	15"-20" Range - Set at 15" 2403216	15"-20" Range - Set at 16"	7/03217	15"-20" Range - Set at 17"	
_	_	15"-20" Range - Set at 16"	☐ Z <del>4</del> U3Z1/	13 -20 halige - Set at 17	
	15"-20" Range - Set at 10"	13 -20 hange - Jet at 19			\$
	gc				τ

	Seat D	epth								
I		Standard Seat Depths (Adjustable)								
	2404016	16" Seat Depth 2404017	17" Seat Depth							
	2404018	18" Seat Depth	19" Seat Depth							
	2404020	20" Seat Depth		\$						
ľ		Custom Seat Depths								
	2404021	21" Seat Depth		\$						
	2404022	22" Seat Depth		\$						
1										
Į	Frame	Colour								
		<b>PDG Premium Colours</b> View colour swatches on	PDG's website. pdgmobility.com/colours							
	2405001	Black Shimmer 2405015	Sky Blue 2405016 Poppy Red							
	2405003	Fine Texture Black 2405010	Lollypop Blue 2405011 Lollypop Red							
	2405017	Arctic Grey 2405018	Tropical Teal 2405019 Tangerine Orange							
	2405020	Olive Green 2405021	Lush Lilac 🔲 2405012 Bubble Gum Pink							
l	2405022	Leaf Green 2405023	Boysenberry Purple							
l	2405200	<b>Custom Colour</b> Contact PDG for specifications.		\$						
I	^									
I	Armre	sts								
l	2406000	No Armrests								
		Height Adjustable Armrests (Single Post)		\$						
l	2406111	8"-11" Range 🔲 2406114	10"-14" Range							
I	2406100	Fixed Height Armrests (12") Full Length Armp	ad only.							
ľ	£	Armrest Height If provided, Armrests will be set to	this height by PDG. If left blank, the default setting will be used.							
	3	Seat Pan to top of Armrest:	Does not include height of Armpad							
ľ	<u> </u>									
	1	Armrest Position Indicate preference for Armrest position. If left blank, the default setting will be used.  In the interest of maintaining chair stabily and avoiding interferance with other chair functions, PDG may not be able to accommodate stated preference.								
	2706401	<u>_</u>	Front							
ı										
ı	Armpa	d s								
		Regular Armpads								
l	2407100	Desk Length - 2" x 10" 2407101	Full Length - 2" x 14"							
I		Waterfall Armpads		\$						
	2407105	Desk Length - 2" x 10" 2407106	Full Length - 2" x 14"							
ľ		Wide Armpads May interfere with wheels in some	tilt configurations.	\$						
	2407110	Desk Length - 3" x 10" 2407111	Full Length - 3" x 12"							
ľ		Gel Armpads May interfere with wheels in some tilt configurations. \$								
	2407120		Full Length - 3.5" x 12"							
ľ		Contour Arm Trough with Hand Pad May in	•	\$						
	2407130		Left (4.5" x 18")							
L										
	Armre	st Options								
ſ		Armrest Wideners Move Armrests outward by up	to 1" on each side. Seat size does not change.							
l	2407210	1" Total Additional Width		\$						
۱	2407211			\$						
l	2407310	Clothing Guards Not compatible with 8"-11" Heigl	nt range.	\$						
ŀ		Armrest Extensions Not compatible with Desk Le		\$						
۱	7407400		3" Extension - Rearward	•						
1		3 Execusion Forward 240/401	- Extension Regivale							

Se	eat P	an																
	2408000	No Se	eat Pa	ın														
	2408001	Solid	Alun	niniun	n Seat	Pan												\$
Se	eat H	leigl	n t															
	Don't forget	Selec	t des	ired S	eat-to	-Floo	r Heig	<b>jht</b> s	TF Heig	jht is adj	ustable	within	the rang	e of the	chosen	Subfra	me Plate (Low/High).	
	lorget					Low							High					
		S	RW	13"	14"	15"	16"	17"	18"	RW	15"	16"	17"	18"	19"	20"		
		Casters	12"				<u></u>	_		12"						_		
		6" Ca	16" 20"				<del></del>			16" 20"								
		9	22"							22"								
			24"							24"								
	ı					_											1	
		Casters	RW	13"	14"	Low 15"	16"	17"	18"	RW	15"	16"	High 17"	18"	19"	20"		
		Cast	16"	13	14					16"	15	10						
		-∞	24"							24"								
	'																	
C	a s t e r	rs																
		Ureth	nane	Caste	rs 8"	Casters	are con	npatible	only w	ith 16″ a	nd 24″ R	Rear Wh	eels.					
	2411061	6" x 1.2	25" Ca	ster siz	e			24110	081 8	" x 1.25	" Caste	r size						
	2411063								\$									
	2411084							\$										
	Pneumatic Casters 8" Casters are compatible only with 16" and 24" Rear Wheels.																	
	2411161	6" x 1.	25" Ca	ster siz	e													\$
	2411181	8" x 1	25" Ca	ster siz	e													\$
	2411184	·								\$								
	2411260	Soft-Roll Casters 6" x 1.50" Caster size. Urethane tire & Silver Anodized Aluminium hub.								\$								
	2411400	Frog Legs Suspension Forks Only compatible with 16 and 24" Rear Wheels. Requires 6" Soft-Roll Caster. \$								\$								
Κŧ	ear V																	
		Comp	osite	Whe	els													
	2412012	12" WI	neel si	ze				24120	016 1	6" Whe	el size					2412020	20" Wheel size	
	2412022	22" WI						24120	024 2	4" Whe	el size							
		Spok	e Wh	eels														\$
	2412120	20" WI	neel si	ze				2412	122 2	2" Whe	el size					2412124	24" Wheel size	
		Rear	Whee	el Posi	tion	Indica	te Rear	Wheel p	osition	ing prefe	erence.	If left bl	ank, the	default	setting	will be	used.	
7			nterest	of main	taining	chair st		_	-					ons, PD	G may n	ot be al	ole to accommodate stated preference.	
Ш	2412401	Rear					L	2412	403 F	ront	Default	Positior	1					
Α:	xle T	уре																
_																		
$\Box$	2413000	Quicl	c Rele	ase R	ear A	des												
		Quick Fixed				cles												
	2413000 2413010	Quick Fixed				cles												
		Fixed	Rear			kles												
R	<sup>2413010</sup> ear T	Fixed	Rear	Axle		des												

Pneumatic Tyres with Flat-Free Inserts May result in a finished Seat Height 1/2" greater than stated. Not available with Spoke Wheels.

Handr	Handrims are only available with 20", 22", and 24" Rear Wheels.	
2415000	No Handrims	
2415010	Standard Aluminium Handrims	
2415020	Plastic Coated Handrims Not compatible with Drum Brakes.	\$
2415030	Projection Handrims Composite Wheels only. 10 Projections, 30°, 1-1.8" Length.	\$
\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\		
wneel	Locks & Brakes	
_	User Wheel Locks	
2416010	Push to Lock	
2416030	Attendant Wheel Locks (Push to Lock)	\$
2416040	User & Attendant Wheel Locks Not compatible with Drum Brakes on 20" Wheels.	\$
2416300	<b>Drum Brakes</b> Available with 12" Composite or 20" Spoke Rear Wheels. Urethane Tires only.	\$
l_	User-activated Unilateral Wheel Lock Pull to Lock.	\$
2416310	Left Activation 2416311 Right Activation	
Wheel	Lock Options	
2416100	Wheel Lock Extensions Not compatible with Attendant Wheel Lock.	\$
2416200	Hill Holders Requires Pneumatic Rear Tires with Flat-Free Inserts.	\$
Anti-T	Tippers	
2417010	Rear Anti-Tippers Required Safety Option.	\$
Back F	Posts	
Dack		
<b>×</b> 2418010	Back Post Style  Stroller Handle Back	
2410010	Back Post Height Measured from the Seat Pan to the Handle.	
2418425	_	
	Back Post Folding Fold-down Back is not compatible with Reclining Backrest, Dynamic Rocker Back and will be substituted with a Non-folding Back.	
2419220	Fold-down	
	Seat to Back Angle	
2419090	_	
2419114	Set at 114°	
Pack (	Options	
Dack		
	Angle/Height Adjustable Stroller Handle Not compatible with Headrest Mounting Plate.	\$
2419010	Button on Outside 2419011 Button on Inside	
	Endomorph Back Backrest will be narrower than Seat by total of 2x the Offset selected below. Minimum width of Backrest is 12".  Not compatible with Dynamic Rocker Back, Reclining Backrest. Requires Straight Back Post.	\$
2418102	1" Offset per side	
2419210	10" Backrest Extension Requires Angle/Height Adjustable Stroller Handle.	\$
2419212	Headrest Mounting Plate	\$
	Not compatible with Backrest Extension, Angle/Height Adjustable Stroller Handle. Not required if mounting to a solid Back.	
2419230	Spring Back Suspension Not compatible with Reclining Back.	\$
2419240	Seating Dynamics Dynamic Rocker Back Interface	\$
	Not compatible with Fold-down Back, Endomorph Back, 30° Recline, Standard Upholstery. Finished Back Post Height is 4" taller than selected Back Post	
<b>(i)</b>	Choose the standard <b>Bentley</b> with a steel frame for highly agitated users. See separate order form.	

Back l	Upholstery	
2420000	No Back Upholstery	
	Standard Upholstery	\$
2420418	Short (18" Height)	
	Tension Adjustable Upholstery Height of Upholstery is 16". Not available with Cane Handle Back.	
2420450	For 14" to 22" Seat Width	\$
2420451	For 23" to 24" Seat Width	\$
	Position of Upholstery Select the desired position of the top of the Upholstery relative to the Seat Pan.	
	22" Back Post 25" Back Post	
		4" 25"
<u></u>		
Tilt A	ctivation	
	Attendant Tilt only Select trigger mounting location below.	
2423011	Right Back Post 2423012 Left Back Post	
2423013	Two Trigger Setup A Trigger mounted on each side of the Stroller Handle. Reduces grip force required to activate tilt. Not compatible with Reclining Backrest, Drum 6	Brakes.
	User Tilt only Full Length Arm Pads only. Select trigger mounting location below.	\$
2423021	Right Armrest   2423022 Left Armrest	
	Attendant & User Tilt Not compatible with Tall (25") Back Post, Reclining Backrest. Full Length Arm Pads only. Select trigger mounting locations below.	\$
2423031	Right Back Post 2423032 Left Back Post	
2423041	Right Armrest	
	Power Tilt 113kg/250 lbs Weight Capacity. 20° tilt range. Includes 2 batteries for off-chair charging. pdgmobility.com/power-tilt	
	Power Tilt is compatible with either O2 Holder or IV Pole on the same chair, not both.	
2423400	Standard Power Tilt	\$
2423410	Power Tilt with Manual Tilt Override Allows for instant manual release of tilt in case of power tilt failure. Minimum Seat Width is 16".	\$
Select	Toggle Switch	
Control Switch	Button Switch	
	Stealth Egg Switch 2423440 Not installed	<u></u>
	Optional for Egg Switch: 2423445 Swing Away Mounting Hardware Not compatible with all Headrest makes and models.  Specify Headrest to be used:	\$
	• •	
Reclin	n e	
2423310	Reclining Backrest (Manual)	\$
	30° maximum recline. Not compatible with Backrest Extension, Fold-down Back, Tension Adjustable Upholstery, Dynamic Rocker Back, Endomorph Back. Requires longer Frame. Maximum Seat Depth is 19". Finished Back Post Height is 3" taller than selected Back Post Height.	
Front	Rigging	
2425000	No Front Rigging 🔲 2425001 Sector Blocks only	
	Easy-Out Front Rigging Effortless insertion and removal. No Hanger Bracket remains on frame. pdgmobility.com/easy-out	
2425410	Fixed 70°	\$
2425420	Universal Angle Adjustable (0°-110°) Set at angle: (use increments of 10°)	\$
	Adjust angle by loosening one bolt. Tool-free leg-length adjustment. Front Rigging can interfere with casters in the 90-110° settings.	
	Optional for Universal AA: 2425421 AA High-mount Option For shorter Lower Leg Lengths of 8"-12.5".	
	Swing Away Front Rigging Legacy Design. Not compatible with Easy-Out.	
2425130	Swing Away 60°	<u>,</u>
2425200	Swing Away Elevating Legrests Includes Calf Pads.	\$
2425300	1" Offset Hangers for Swing Away	\$
2425110	Standard Plug In 70° Front Rigging Legacy Design. Not compatible with Easy-Out.	

Footp	lates	
2426010	Composite Footplates	
☐ 2426020	Aluminium Angle Adjustable Footplates	\$
2426030	One Piece Fixed Footplate  Available on Plug In Front Rigging only. Requires selection of Composite or Aluminium Angle Adjustable.	\$
2426040	One Piece Flip-up Footplate Requires selection of Composite or Aluminium Angle Adjustable.	\$
2426050	Interlocking Angle Adjustable Footplates Available for Seat Widths up to 21" only.	\$
2420030	Available for Seat Wildtis up to 21 only.	
Footre	est/Legrest Accessories	
	Calf Pads Not compatible with Gel Padding.	
2427012	For Easy-Out Front Rigging Includes reinforced premium Calf Pad mount.	\$
2427010	For Swing Away Front Rigging	\$
2427020	<b>Gel Padding</b> Not compatible with Calf Pad or Easy-Out Front Rigging.	\$
	Gel Knee Pads	
2427032	For Easy-Out Angle Adjustable Front Rigging	\$
2427030	For Swing Away ELR Front Rigging	\$
2427040	Length Adjustable Heel Loops	\$
2427050	Bodypoint Padded Calf Strap	\$
Front	Rigging Extension Tubes	
TTOTIC		
7439010	Regular Extension Tubes No selection required for Easy-Out AA High-mount Option.  Short 14" 10" for Easy Out Examt Display 12" 17" for Suring Augus and Chandrard Display In Examt Display	
2428010 2428020	Short 14"-18" for Easy-Out Front Rigging 13"-17" for Swing Away and Standard Plug In Front Rigging  Long 18"-24" for Easy-Out Front Rigging 15"-19" for Swing Away and Standard Plug In Front Rigging	\$
2428020	Lower Leg Length If provided, Front Rigging will be set to this length by PDG. If left blank, the default setting will be used.	
4		
	Seat Pan to Foot Plates: Measured along the length of the Front Rigging. Consider the height of your Seat Cushion.	
Misce	llaneous Options	
	Spoke Guards Available for 20"-24" Composite Rear Wheels. Made from durable and lightweight aluminum.	\$
2430020	Black 2430021 Frame Color	
2430050	Protective Lower Padding	\$
	Stealth Flip Down Abductor Includes wedge-style pad. Requires Solid Seat Pan.	\$
2430060	Small Pad 3"x4"x3"x2" size	
2430080	Gel Hip Guides Reduces available Seat Width by 2".	\$
2430110	IV Pole Not compatible with Attendant Wheel Locks.	\$
2430120	O2 Holder Not compatible with Attendant Wheel Locks.	\$
2430200	Q'Straint Lap Belt Model S5-6329-11. For use with WC-19 Transit Tie Down System. 24"-51" Belt Length.	\$
2430222	Medical Necessities Backpack Black with Permobil Logo.	\$
2430169	Rubber Shroud for Caster Journals	\$
2430170	Adhesive Back Hook Strip, 2" x 30" For Cushion mounting.	\$
	The Free Control of the State o	