# PDG BENTLEY LT-R

January 1, 2024

Customer and Order Information			
Purchase Order *	Tag		
Dealer/Provider Name *			
Purchaser Name and Contact Information *			
Shipping Address *			
	kac Hoight		* required
User Information ( <i>if available</i> ) Weight	kgs Height	_ cm	* required
Order Notes/Instructions			
Base Chair			
Bentley LT-R 20° Manual Tilt Wheelchair	Reverse Wheel Layout enhances user acce	ss for self-propulsion. pdgmobility.com/blt-r	
BENTLEY-LTR Bentley LT-R 20° Manual Tilt Wheelchair			\$
Choose the standard <b>Bentley</b> with a steel fra	me for agitated or heavier users.	See separate order form.	
Frame Type & Weight Capacity			
Frame Type All frames offer 136kg/300 lbs Weight	Capacity		
□ 2702010 Fixed Width Frame Select a Fixed Seat Width below.			
□ 2702025 Adjustable Width Frame Select an Adjustable Seat V	Vidth below.		\$
User Weight Range Required for setup of tilt up	ift force.		
□ 2702430 Up to 34kg/75 lbs □ 2702431	34kg/75 lbs to 45kg/100 lbs	2702432 45kg/100 lbs to 52kg/115 lbs	
□ 2702433 52kg/115 lbs to 68kg/150 lbs □ 2702434	68kg/150 lbs to 90kg/200 lbs	2702435 90kg/200 lbs to 113kg/250 lbs	
2702436 113kg/250 lbs to 136kg/300 lbs			
Frame Options			
2702300 Transit Tie Down System (TTDS)			
TTDS includes 4 factory-installed transport brackets. TTDS	has been tested according to ANSI/RESNA	WC 19. See Owners Manual for complete details.	
Seat Width		Overall chair width is +10.5".	
Fixed Seat Widths Order with Fixed Frame.			
2703015 15" Seat Width 2703016	16" Seat Width	2703017 17" Seat Width	
2703018 18" Seat Width 2703019	19" Seat Width		
2703020 20" Seat Width 2703021	21" Seat Width	2703022 22" Seat Width	\$
2703023 23" Seat Width			\$
2703024 24" Seat Width			\$
Adjustable Seat Widths Order with Adjustable	Frame.		
2703112 12"-16" Range - Set at 12" 2703113	12"-16" Range - Set at 13"	2703114 12"-16" Range - Set at 14"	
2703115 12"-16" Range - Set at 15" 2703116	12"-16" Range - Set at 16"		
2703215 15"-20" Range - Set at 15"  2703216	15"-20" Range - Set at 16"	2703217 15"-20" Range - Set at 17"	
2703218 15"-20" Range - Set at 18" 2703219	15"-20" Range - Set at 19"		
2703220 15"-20" Range - Set at 20"			\$

Seat D	) e p t h						
	Standard Seat Depths (Adju	stable)					
2704016	16" Seat Depth	2704017	17" Seat Depth				
2704018	18" Seat Depth	2704019	19" Seat Depth				
2704020	20" Seat Depth						\$
	Custom Seat Depths						
2704021	21" Seat Depth						\$
2704022	22" Seat Depth						\$
<b>Г</b> и о ио о	Colour						
Frame	Colour						
	PDG Premium Colours View	_		dgmobility.com/colours			
2705001	Black Shimmer	2705015	Sky Blue		2705016	Poppy Red	
2705003	Fine Texture Black	2705010	Lollypop Blue		2705011	Lollypop Red	
2705017	Arctic Grey	2705018	Tropical Teal		2705019	Tangerine Orange	
2705020	Olive Green	2705021	Lush Lilac		2705012	Bubble Gum Pink	
2705022	Leaf Green	2705023	Boysenberry Purple		2705014	Daffodil Yellow	
2705200	Custom Colour Contact PDG fo	r specifications.					\$
Armre	sts						
2706000	No Armrests						
		(Cincels De at)					A
	Height Adjustable Armrests	-	10" 14" Dan an	_	2706446	1011 1011 Decement	\$
2706111	8"-11" Range		10"-14" Range		2706116	12"-16" Range	
2706100	Fixed Height Armrests (12")						
1	Armrest Height If provided, Ar	mrests will be set			tting will b	be used.	
	Seat Pan to top of Armrest:		Does not include heig				
J.	Armrest Position Indicate pre						
2706401	In the interest of maintaining chair stal Rear Default Position	bily and avoiding ii		hair functions, PDG may	not be ab	le to accommodate stated preference.	
2700401	hear belaat rostion	2700405	Hone				
A r m p a	l d s						
	Regular Armpads						
2707100	Desk Length - 2" x 10"	2707101	Full Length - 2" x 14	."			
	Waterfall Armpads						\$
2707105	Desk Length - 2" x 10"	2707106	Full Length - 2" x 14	."			
	Wide Armpads May interfere w	vith wheels in som	e tilt configurations.				\$
2707110	Desk Length - 3" x 10"	2707111	Full Length - 3" x 12				
	Gel Armpads May interfere wit	h wheels in some t	ilt configurations.				\$
2707120	Full Length - 2" x 12"	2707121	Full Length - 3.5" x	12"			
	Contour Arm Trough with H	and Pad May	interfere with wheels ir	some tilt configurations	5.		\$
2707130	Right (4.5" x 18")		Left (4.5" x 18")	-			
Armre	st Options						
	Armrest Wideners Move Arm	rests outward by u	ıp to 1" on each side. Se	at size does not change.			
2707210	1" Total Additional Width						\$
2707211	2" Total Additional Width						\$
2707310	Clothing Guards Not compati	ble with 8"-11" Hei	ght range.				\$
	Armrest Extensions Not com	patible with Desk	Length Armpads.				\$
2707400	3" Extension - Forward	2707401	3" Extension - Rearv	vard			

2708000 No Seat Pan

#### **2708001** Solid Aluminium Seat Pan

#### Seat Height

> Don't forget	Seleo	t desi:	red S	eat-to	-Floo	r Heig	<b>ht</b> s	TF Heig	ht is adj	ustable	within t	he rang	e of the	choser	Subfra
					Low							High			
	ers	RW	12"	13"	14"	15"	16"	17"	RW	14"	15"	16"	17"	18"	19"
	Casters	20"							20"						
	6"	22"							22"						
		24"							24"						
	ters				Low							High			
	Casters	RW	12"	13"	14"	15"	16"	17"	RW	14"	15"	16"	17"	18"	19"
	- 80	24"							24"						

## Casters

	Urethane Casters	8" Casters are compatible only with 24" Large Wheels.	
2711061	6" x 1.25" Caster size	2711081 8" x 1.25" Caster size	
2711063	6" x 1.50" Caster size		\$
2711084	8" x 2.00" Caster size		\$
	Pneumatic Casters	8" Casters are compatible only with 24 <sup>°</sup> Large Wheels.	
2711161	6" x 1.25" Caster size		\$
2711181	8" x 1.25" Caster size		\$
2711184	8" x 2.00" Caster size		\$
2711260	Soft-Roll Casters	6" x 1.50" Caster size. Urethane tire & Silver Anodized Aluminium hub.	\$
2711400	Frog Legs Suspens	sion Forks Only compatible with 24" Large Wheels. Requires 6" Soft-Roll Caster.	\$

## Large Wheels

	Composite Wheels				
2712020	20" Wheel size	2712022	22" Wheel size	2712024 24" Wheel size	
	Spoke Wheels				\$
2712120	20" Wheel size	2712122	22" Wheel size	2712124 24" Wheel size	
J.	Large Wheel Position Indic	ate Large Wheel pos	itioning preference. If left b	lank, the default setting will be used.	
	In the interest of maintaining chair sta	abily and avoiding ir	terferance with other chair	functions, PDG may not be able to accommodate stated preference.	
2712401	Rear Less stable	2712402	Mid Default Position	2712403 Front More stable. Not compatible with 20"-22"	Seat Depth.

Axle T	уре
2713000	Quick Release Axles
2713010	Fixed Axles

Large Tyres	
2714000 Urethane Tyres	
2714010       Pneumatic Tyres       May result in a finished Seat Height 1/2" greater than stated.	\$
2714020 Pneumatic Tyres with Flat-Free Inserts May result in a finished Seat Height 1/2" greater than stated. Not available with Spoke Wheels.	\$
Handrims	
2715000 No Handrims	
2715010 Standard Aluminium Handrims	
2715020 Plastic Coated Handrims	\$

#### 2715030 **Projection Handrims** Composite Wheels only. 10 Projections, 30°, 1-1.8" Length.

\$

Whee	l Locks & Brakes	
	User Wheel Locks	
2716010	Push to Lock 🛛 2716020 Pull to Lock	
	User-activated Unilateral Wheel Lock Pull to Lock.	\$
1016310	Left Activation 🗌 1016311 Right Activation	
Wheel	l Lock Options	
2716100	Wheel Lock Extensions	\$
2716200	Hill Holders Requires Pneumatic Large Tires with Flat-Free Inserts.	\$
Anti-1	Lippers .	
	Front Anti-Tippers Required Safety Option. Must choose one type.	
2717010		\$
2717015	Spring-loaded Dampens the forward-tip movement of the chair during transfers and allows for improved ground clearance. Not removable.	\$
Backl	Posts	
	Back Post Style	
2718010	-	
	Back Post Height Measured from the Seat Pan to the Handle.	
2718425	Short (22") 2718431 Tall (25")	
	Back Post Folding Fold-down Back is not compatible with Reclining Backrest, Dynamic Rocker Back and will be substituted with a Non-folding Back.	
2719220	Fold-down	
	Seat to Back Angle Seat Angles above 98° may cause interference at Seat Depths above 19".	
2719090	Set at 90°         2719098         Set at 98°         2719106         Set at 106°	
	Set at 90°         I         2719098         Set at 98°         I         2719106         Set at 106°           Set at 114°         I         2719122         Set at 122°         Set at 122°         Set at 122°	
2719114		
2719114	Set at 114° 2719122 Set at 122°	\$
2719114	Set at 114°         2719122         Set at 122°           Options         Set at 122°         Set at 122°	\$
□ 2719114 Back (	Set at 114° 2719122 Set at 122°   Options   Angle/Height Adjustable Stroller Handle   Not compatible with Headrest Mounting Plate.	\$
Back (	Set at 114° 2719122 Set at 122°     Options     Angle/Height Adjustable Stroller Handle Not compatible with Headrest Mounting Plate.   Button on Outside 2719011   Button on Inside   Endomorph Back Backrest will be narrower than Seat by total of 2x the Offset selected below. Minimum width of Backrest is 12".   Not compatible with Dynamic Rocker Back, Reclining Backrest. Requires Straight Back Post.	
<ul> <li>□ 2719114</li> <li>B a c k (0)</li> <li>□ 2719010</li> <li>□ 2718102</li> </ul>	Set at 114° 2719122 Set at 122°   Options  Angle/Height Adjustable Stroller Handle Not compatible with Headrest Mounting Plate. Button on Outside 2719011 Button on Inside  Endomorph Back Backrest will be narrower than Seat by total of 2x the Offset selected below. Minimum width of Backrest is 12". Not compatible with Dynamic Rocker Back, Reclining Backrest. Requires Straight Back Post. 1" Offset per side 2718103 1.5" Offset per side 2718104 2" Offset per side	\$
<ul> <li>□ 2719114</li> <li>Back (0)</li> <li>□ 2719010</li> <li>□ 2718102</li> <li>□ 2719210</li> </ul>	Set at 114° 2719122 Set at 122°     Options     Angle/Height Adjustable Stroller Handle Not compatible with Headrest Mounting Plate.   Button on Outside 2719011   Button on Inside   Endomorph Back Backrest will be narrower than Seat by total of 2x the Offset selected below. Minimum width of Backrest is 12".   Not compatible with Dynamic Rocker Back, Reclining Backrest. Requires Straight Back Post.   1" Offset per side 2718103   1.5" Offset per side 2718104   2" Offset per side   IO" Backrest Extension Requires Angle/Height Adjustable Stroller Handle.	\$
<ul> <li>□ 2719114</li> <li>B a c k (0)</li> <li>□ 2719010</li> <li>□ 2718102</li> </ul>	Set at 114° 2719122 Set at 122°   Options   Angle/Height Adjustable Stroller Handle Not compatible with Headrest Mounting Plate.   Button on Outside 2719011 Button on Inside   Endomorph Back Backrest will be narrower than Seat by total of 2x the Offset selected below. Minimum width of Backrest is 12".   Not compatible with Dynamic Rocker Back, Reclining Backrest. Requires Straight Back Post.   1" Offset per side 2718103   1.5" Offset per side 2718104   2718105 Yeight Adjustable Stroller Handle.	\$
<ul> <li>□ 2719114</li> <li>Back (0)</li> <li>□ 2719010</li> <li>□ 2718102</li> <li>□ 2719210</li> </ul>	Set at 114° 2719122 Set at 122°   Options   Angle/Height Adjustable Stroller Handle Not compatible with Headrest Mounting Plate.   Button on Outside 2719011 Button on Inside   Endomorph Back Backrest will be narrower than Seat by total of 2x the Offset selected below. Minimum width of Backrest is 12".   Not compatible with Dynamic Rocker Back, Reclining Backrest. Requires Straight Back Post.   1" Offset per side 2718103   1.5" Offset per side 2718104   2" Offset per side 2718103   1.5" Offset per side 2718104   2" Offset per side 2000000000000000000000000000000000000	\$
<ul> <li>□ 2719114</li> <li>B a c k (0)</li> <li>□ 2719010</li> <li>□ 2718102</li> <li>□ 2719210</li> <li>□ 2719212</li> </ul>	Set at 114° 2719122 Set at 122°   Options   Angle/Height Adjustable Stroller Handle Not compatible with Headrest Mounting Plate.   Button on Outside 2719011 Button on Inside   Endomorph Back Backrest will be narrower than Seat by total of 2x the Offset selected below. Minimum width of Backrest is 12".   Not compatible with Dynamic Rocker Back, Reclining Backrest. Requires Straight Back Post.   1" Offset per side 2718103   1.5" Offset per side 2718104   2718105 Yeight Adjustable Stroller Handle.	\$ \$ \$
<ul> <li>□ 2719114</li> <li>Back</li> <li>□ 2719010</li> <li>□ 2718102</li> <li>□ 2719210</li> <li>□ 2719212</li> <li>□ 2719212</li> <li>□ 2719230</li> </ul>	Set at 114° 2719122 Set at 122°     Options     Angle/Height Adjustable Stroller Handle Not compatible with Headrest Mounting Plate.   Button on Outside 2719011   Button on Inside   Endomorph Back Backrest will be narrower than Seat by total of 2x the Offset selected below. Minimum width of Backrest is 12".   Not compatible with Dynamic Rocker Back, Reclining Backrest. Requires Straight Back Post.   1" Offset per side 2718103   1.5" Offset per side 2718104   2" Offset per side 2718103   1.5" Offset per side 2718104   2" Offset per side 10" Backrest Extension Requires Angle/Height Adjustable Stroller Handle.   Headrest Mounting Plate   Not compatible with Backrest Extension, Angle/Height Adjustable Stroller Handle. Not required if mounting to a solid Back.   Spring Back Suspension	\$ \$ \$ \$ \$
<ul> <li>□ 2719114</li> <li>Back</li> <li>□ 2719010</li> <li>□ 2718102</li> <li>□ 2719210</li> <li>□ 2719212</li> <li>□ 2719212</li> <li>□ 2719230</li> </ul>	Set at 114° 2719122 Set at 122°     Options     Angle/Height Adjustable Stroller Handle Not compatible with Headrest Mounting Plate.   Button on Outside 2719011   Button on Inside   Endomorph Back Backrest will be narrower than Seat by total of 2x the Offset selected below. Minimum width of Backrest is 12".   Not compatible with Dynamic Rocker Back, Reclining Backrest. Requires Straight Back Post.   1" Offset per side 2718103   1.S" Offset per side 2718104   2" Offset per side 2718103   1.S" Offset per side 2718104   2" Offset per side 2718104   10" Backrest Extension Requires Angle/Height Adjustable Stroller Handle.   Headrest Mounting Plate   Not compatible with Backrest Extension, Angle/Height Adjustable Stroller Handle. Not required if mounting to a solid Back.   Spring Back Suspension Not compatible with Reclining Back.   Seating Dynamics Dynamic Rocker Back Interface	\$ \$ \$ \$ \$
<ul> <li>□ 2719114</li> <li>B a c k (0)</li> <li>□ 2719010</li> <li>□ 2718102</li> <li>□ 2719210</li> <li>□ 2719212</li> <li>□ 2719230</li> <li>□ 2719240</li> <li>① ①</li> </ul>	Set at 114° 2719122 Set at 122°     Options     Angle/Height Adjustable Stroller Handle Not compatible with Headrest Mounting Plate.   Button on Outside 2719011   Button on Inside     Endomorph Back   Backrest will be narrower than Seat by total of 2x the Offset selected below. Minimum width of Backrest is 12".   Not compatible with Dynamic Rocker Back, Reclining Backrest. Requires Straight Back Post.   1° Offset per side 2718103   10" Backrest Extension   Requires Angle/Height Adjustable Stroller Handle.   Headrest Mounting Plate   Not compatible with Backrest Extension, Angle/Height Adjustable Stroller Handle. Not required if mounting to a solid Back.   Spring Back Suspension   Not compatible with Fold-down Back, Extension Back.   Seating Dynamic Rocker Back Interface Not compatible with Fold-down Back, 50° Recline, Standard Upholstery. Finished Back Post Height is 4" taller than selected Back Post	\$ \$ \$ \$ \$
<ul> <li>□ 2719114</li> <li>B a c k (0)</li> <li>□ 2719010</li> <li>□ 2718102</li> <li>□ 2719210</li> <li>□ 2719212</li> <li>□ 2719230</li> <li>□ 2719240</li> <li>① ①</li> </ul>	Set at 114° 2719122 Set at 122°   Options   Angle/Height Adjustable Stroller Handle Not compatible with Headrest Mounting Plate.   Button on Outside 2719011 Button on Inside   Endomorph Back Backrest will be narrower than Seat by total of 2x the Offset selected below. Minimum width of Backrest is 12".   Not compatible with Dynamic Rocker Back, Reclining Backrest. Requires Straight Back Post. 2718103   1" Offset per side 2718103   10" Backrest Extension Requires Angle/Height Adjustable Stroller Handle.   Headrest Mounting Plate   Not compatible with Backrest Extension, Angle/Height Adjustable Stroller Handle. Not required if mounting to a solid Back.   Spring Back Suspension   Not compatible with Fold-down Back, Endomorph Back, 30" Recline, Standard Upholstery. Finished Back Post Height is 4" taller than selected Back Post   Choose the standard Bentley with a steel frame for highly agitated users.	\$ \$ \$ \$ \$
<ul> <li>□ 2719114</li> <li>B a c k</li> <li>□ 2719010</li> <li>□ 2719010</li> <li>□ 2719210</li> <li>□ 2719212</li> <li>□ 2719220</li> <li>□ 2719240</li> <li>①</li> <li>①</li> <li>①</li> <li>B a c k</li> </ul>	Set at 114° 2719122 Set at 122°   Options   Angle/Height Adjustable Stroller Handle Not compatible with Headrest Mounting Plate.   Button on Outside 2719011 Button on Inside   Endomorph Back Backrest will be narrower than Seat by total of 2x the Offset selected below. Minimum width of Backrest is 12".   Not compatible with Dynamic Rocker Back, Reclining Backrest. Requires Straight Back Post. 2718104   1" Offset per side 2718103   1.5" Offset per side 2718104   10" Backrest Extension Requires Angle/Height Adjustable Stroller Handle.   Headrest Mounting Plate Not compatible with Backrest Extension, Angle/Height Adjustable Stroller Handle. Not required if mounting to a solid Back.   Spring Back Suspension Not compatible with Reclining Back.   Seating Dynamics Dynamic Rocker Back Interface   Not compatible with Fold-down Back, 30° Recline, Standard Upholstery. Finished Back Post Height is 4" taller than selected Back Post   Choose the standard Bentley with a steel frame for highly agitated users.   Separate order form.	\$ \$ \$ \$ \$
<ul> <li>□ 2719114</li> <li>B a c k</li> <li>□ 2719010</li> <li>□ 2719010</li> <li>□ 2719210</li> <li>□ 2719212</li> <li>□ 2719220</li> <li>□ 2719240</li> <li>①</li> <li>①</li> <li>①</li> <li>B a c k</li> </ul>	Set at 114° 2719122 Set at 122°   Options   Angle/Height Adjustable Stroller Handle Not compatible with Headrest Mounting Plate.   Button on Outside 2719011 Button on Inside   Endomorph Back Backrest will be narrower than Seat by total of 2x the Offset selected below. Minimum width of Backrest is 12".   Not compatible with Dynamic Rocker Back, Reclining Backrest. Requires Straight Back Post. 2718104 2" Offset per side   1° Offset per side 2718103 1.5" Offset per side 2178104 2" Offset per side   10" Backrest Extension Requires Angle/Height Adjustable Stroller Handle. 2   Meadrest Mounting Plate Not compatible with Backrest Extension, Angle/Height Adjustable Stroller Handle. Not required if mounting to a solid Back.   Spring Back Suspension Not compatible with Reclining Back.   Seating Dynamics Dynamic Rocker Back Interface   Not compatible with Fold-down Back, Endomorph Back, 30" Recline, Standard Upholstery. Finished Back Post Height is 4" taller than selected Back Post   Choose the standard Bentley with a steel frame for highly agitated users. See separate order form.   Up holstery No Back Upholstery	\$ \$ \$ \$ \$
<ul> <li>□ 2719114</li> <li>B a c k (0)</li> <li>□ 2719010</li> <li>□ 2719010</li> <li>□ 2719210</li> <li>□ 2719210</li> <li>□ 2719220</li> <li>□ 2719240</li> <li>① 2719240</li> <li>① 2720000</li> </ul>	Set at 114° 2719122 Set at 122°   Options   Angle/Height Adjustable Stroller Handle Not compatible with Headrest Mounting Plate.   Button on Outside 2719011 Button on Inside   Endomorph Back Backrest will be narrower than Seat by total of 2x the Offset selected below. Minimum width of Backrest is 12".   Not compatible with Dynamic Rocker Back, Reclining Backrest. Requires Straight Back Post. 2718104 2" Offset per side   10" Backrest Extension Requires Angle/Height Adjustable Stroller Handle.   Headrest Mounting Plate   Not compatible with Backrest Extension, Angle/Height Adjustable Stroller Handle. Not required if mounting to a solid Back.   Spring Back Suspension   Not compatible with Fold-down Back, Endomorph Back, 30" Recline, Standard Upholstery. Finished Back Post Height is 4" taller than selected Back Post   Choose the standard Bentley with a steel frame for highly agitated users.   See tandard Upholstery   Not Back Upholstery	\$ \$ \$ \$ \$
<ul> <li>□ 2719114</li> <li>B a c k (0)</li> <li>□ 2719010</li> <li>□ 2719010</li> <li>□ 2719210</li> <li>□ 2719210</li> <li>□ 2719220</li> <li>□ 2719240</li> <li>① 2719240</li> <li>① 2720000</li> </ul>	Set at 114° 2719122 Set at 122°   Options   Angle/Height Adjustable Stroller Handle Not compatible with Headrest Mounting Plate.   Button on Outside 2719011 Button on Inside   Endomorph Back Backrest will be narrower than Seat by total of 2x the Offset selected below. Minimum width of Backrest is 12".   Not compatible with Dynamic Rocker Back, Reclining Backrest. Requires Straight Back Post. 2718104 2" Offset per side   1" Offset per side 2718103 1.5" Offset per side 2718104 2" Offset per side   10" Backrest Extension Requires Angle/Height Adjustable Stroller Handle.   Headrest Mounting Plate   Not compatible with Backrest Extension, Angle/Height Adjustable Stroller Handle. Not required if mounting to a solid Back.   Spring Back Suspension   Not compatible with Rold-down Back, Endomorph Back, 30" Recline, Standard Upholstery. Finished Back Post Height is 4" taller than selected Back Post   Choose the standard Bentley with a steel frame for highly agitated users.   See aparte order form.   Up holstery Short (18" Height)   2720421 Regular (21" Height)	\$ \$ \$ \$ \$

See next page for more options >

	<b>D</b> (11																				
	Position of U	phoist	ery				ition of	the top	of the L	pholster	y relative	to the Seat	Pan.								
					ick Pos						_					ack Po					
	Style	17"	18"	19"	20"	21"	22"	23"	24"	25"	_	Style	17"	18"	19"	20"	21"	22"	23"	24"	25"
	Short Regular					<u> </u>					_	Short Regulai									
	Tension Adj	-										Tall									
												Tension A	dj								
Tilt A	ctivation																				
	Attendant Til	t only	Selec	t triggei	mount	ing loc	ation b	elow.													
2723011	Right Back Post				27	23012	Left E	Back Pc	ost												
2723013	Two Trigger Set	up A <sup>-</sup>	Trigger ı	mounted	l on eac	h side	of the S	troller H	landle.	Reduces	grip force	e required to	o activate til	t. Not co	mpatib	le with	Reclinin	ig Backr	est, Dru	m Brak	es.
	User Tilt only	Full L	.ength A	Arm Pade	only. S	elect tr	rigger m	nounting	g locatio	on below										\$	
2723021	Right Armrest				27	23022	Left /	Armres	t												
	Attendant &	User T	ilt No	ot compa	itible wi	th Tall	(25") Ba	ck Post,	, Reclini	ng Backr	est. Full L	ength Arm	Pads only. S	elect trig	jger mo	unting	locatior	ns belov	v.	\$	
2723031	Right Back Post				27	23032	Left E	Back Pc	ost												
2723041	Right Armrest				27	23042	Left /	Armres	t												
	Power Tilt	13kg/25	0 lbs We	eight Ca	oacity. 2	:0° tilt r	range. Ir	ncludes	2 batter	ies for of	f-chair ch	arging. po	dgmobility.c	om/pow	ver-tilt						
	Power Tilt is comp	atible w	ith eithe	er O2 Hol	der or I	V Pole	on the s	ame ch	air, not	both. No	t availabl	e for 12" ST	F Height.								
2723400	Standard Power	Tilt																		\$	
2723410	Power Tilt with I	Manual	Tilt Ov	erride	Allows	for in:	stant m	anual re	lease o	f tilt in ca	se of pow	ver tilt failur	e. Minimum	Seat Wi	dth is 1	6".				\$	
Select	Toggle Sv	witch			27	23421	Insta	lled on	Right	side		27	23422 Inst	alled o	n Left :	side					
> Control	Button Sv	vitch			27	23431	Insta	lled on	Right	side		27	23432 Inst	alled o	n Left :	side					
Switch	Stealth E	gg Swit	ch		27	23440	Not i	nstalle	d												
	Opt	ional for	Egg Sw	itch:	27	23445	Swin	g Away	/ Mour	iting Ha	rdware	Not comp	atible with a	all Headı	rest mal	kes and	models			\$	
								Sp	pecify He	eadrest to	be used:										
Reclin	e																				
_				D																	
2723310	Reclining Bac		-	-						<b>-</b> ·	A 11									\$	
	30° maximum recli Requires longer Fr											•			васк, Е	naomo	rpn вас	к.			
Front	Rigging																				
2725000	No Front Rigg	ging																			
	Easy-Out From	nt Rige	ging	Effortle	ss inser	tion an	nd remo	val. No	Hanger	Bracket ı	remains o	n frame.	odgmobility	.com/ea	<u>sy-out</u>						
2725410	Fixed 70° Not a	available	for 12"	STF Heig	ht.															\$	
2725420	Universal Angle	Adjusta	able (0°	°-110°)		S	Set at ar	ngle:		_ (use ir	ncrement	s of 10°)	12" STF Heig	ght is on	ly comp	oatible v	vith 0°-6	50°.		\$	
	Adjust angle by lo	osening	one bol	t. Tool-fr																	
	Optional for U	Jniversa	I AA:		27	25421	AA H	igh-mo	ount O	ption	For short	er Lower Le	g Lengths o	f 8"-12.5	".						
2725110	Standard Plu	g in 70	)° Froi	nt Rigg	ging	Legac	cy Desig	n. Not c	compati	ble with	Easy-Out.										
Footp	lates																				
2726010	Composite Fo	otpla	tes																		

2726010	Composite Footplates	
2726020	Aluminium Angle Adjustable Footplates	\$
2726030	<b>One Piece Fixed Footplate</b> Available on Plug In Front Rigging only. Requires selection of Composite or Aluminium Angle Adjustable.	\$
2726040	One Piece Flip-up Footplate Requires selection of Composite or Aluminium Angle Adjustable.	\$
2726050	Interlocking Angle Adjustable Footplates Available for Seat Widths up to 21" only.	\$

Footr	est/Legrest Accessories	
2727012	Calf Pads Includes reinforced premium Calf Pad mount.	\$
2727032	Gel Knee Pads Compatible with Universal Angle Adjustable Front Rigging only.	\$
2727040	Length Adjustable Heel Loops	\$
2727050	Bodypoint Padded Calf Strap	\$

## Front Rigging Extension Tubes

	Regular Extension Tubes No selection required for Easy-Out AA High-mount Option.	
2728010	Short <u>14"-18"</u> for Easy-Out Front Rigging <u>13"-17"</u> for Standard Plug In Front Rigging	
2728020	Long <u>18"-24"</u> for Easy-Out Front Rigging <u>15"-19"</u> for Standard Plug In Front Rigging	\$
£	Lower Leg Length If provided, Front Rigging will be set to this length by PDG. If left blank, the default setting will be used.	
1	Seat Pan to Foot Plates: Measured along the length of the Front Rigging. Consider the height of your Seat Cushion.	

### Miscellaneous Options

	Spoke Guards Made from durable and lightweight aluminum.	\$
2730020	Black 🗋 2730021 Frame Color	
2730050	Protective Lower Padding	\$
	Stealth Flip Down Abductor Includes wedge-style pad. Requires Solid Seat Pan.	\$
2730060	Small Pad 3"x4"x3"x2" size 🗌 2730062 Large Pad 5"x5"x4"x3" size	
2730080	Gel Hip Guides Reduces available Seat Width by 2".	\$
2730110	IV Pole	\$
2730120	O2 Holder	\$
2730200	<b>Q'Straint Lap Belt</b> Model S5-6329-11. For use with WC-19 Transit Tie Down System. 24"-51" Belt Length.	\$
2730222	Medical Necessities Backpack Black with Permobil Logo.	\$
2730169	Rubber Shroud for Caster Journals	\$
2730170	Adhesive Back Hook Strip, 2" x 30" For Cushion mounting.	\$